


RELEASED FOR PRODUCTION

SECTION A-A



NOTE 1:

- The connector is designed for the female contacts : Sicma 2/3 1.5 x 0.8 mm.
Sicma 2 2.8 x 0.8 mm.

External gasket maximum clearance after mating male and female holder.


- Completed by the contacts it can be mated with the relative male holder 34 ways : DTBMHPE34BKXXXX
DTBMHPE34DGXXXX

- For use and mating operation : see spec. IPS 160

NOTE 2:

- The connector can be supplied with different slides.
(View "X" shows the alternative configuration)

View "X"
Scale 1:1



Description : DOOR TO BODY 34 WAYS
ASSY FEMALE HOLDER

Cat. No : SEE TABLE

Draft *[Signature]* Vo

Date 10/11/03

We reserve the right to change dimensions or requirements without prior notice.

This is our exclusive property. It is not to be copied, reprinted or disclosed to a third party, nor used for manufacturing, without our written consent, and has to be returned to us in case of no usage.

European projection

Not to scale
All dimensions in mm
Tolerances ± --- mm
Unless otherwise specified



FRAMATOME CONNECTORS INTERNATIONAL

Framatome connectors Italia S.p.A.

FSA 309026
customer drawing

Rev.
09

SHEET
1 OF 2

FSA 309026

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[DTBFHPE34BS](#) [DTBFHPE34BS-B](#)