



SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	23
	LAST NO. USED	19

MISSING SYMBOLS		
7	10-12	15-16


DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P						
09AU04	R	01	-	-	CLEARED REV COLUMN. UPDATED FORMAT & MATERIAL SPEC. REVISED DIM ON TOD.	257803	LLJ	LLJ	LN
04DE07	R	02	-	-	REVISED MAT'L SPEC	403183	MH	MH	JCC
18JA08	R	03	-	-	ALL PARTS UPDATED PDM ATRIBUTES, ADDED DIM C TO PD, UPDATED PD TAXI CHART	403584	MH	PYP	MH
05DE08	R	04	-	-	ALL PARTS - MAT'L SPEC WAS POLYPROPYLENE	406973	JBD	AUG	RAP
02JN09	R	05	-	-	ALL PARTS - MAT'L CALLOUT WAS POLYAMIDE COMPOUND PURPLE AND REVISED GRAPHICS	408110	ESC	GLG	DGL
13JL09	R	06	-	-	ALL PARTS - ADDED DIMENSION 3X B+0/-0.15 NO DRAFT AND COLUMN B TO CHART	408310	CBG	JVM	RAP
30SE09	R	07	-	-	ALL PARTS - B 0/-0.15 NO DRAFT WAS 3X B 0/-0.15 NO DRAFT	409065	EVV	EVV	RAP




TYPE 103
SAME AS TYPE 102
EXCEPT AS SHOWN





TYPE 104
SAME AS TYPE 102
EXCEPT AS SHOWN






TYPE 105
SAME AS TYPE 102
EXCEPT AS SHOWN



TYPE 106
SAME AS TYPE 102
EXCEPT AS SHOWN



TYPE 102



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- THIS PART IS CONTROLLED FOR AUTOMATIC FEEDING AS DENOTED ON DRAWING WITH ▲.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR - SEE CHART
- (2.3)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED" OR NO LOGO.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.

15326937 / ID404318	07	AB	-	106	0.923	15326828 / ID404329 & 15326832 / ID404324	32.89	30.53
15326824 / ID404319	07	AB	-	105	0.790	15326821 / ID404330 & 15326826 / ID404325	28.39	26.03
15326817 / ID404321	07	AB	-	104	0.657	15326814 / ID404331 & 15326819 / ID404326	23.89	21.53
15326810 / ID404322	07	AB	-	103	0.524	15326807 / ID404332 & 15326812 / ID404327	19.39	17.03
15326803 / ID404323	07	AB	-	102	0.391	15326800 / ID404333 & 15326805 / ID404328	14.89	12.53
PART NO	REV	N/P	STATUS	TYPE	VOL CM³	MATING CONNECTOR	A	B

DIMENSIONAL RANGE (MM)		CHART		ET
FROM	TO	> 0	> 20	
		> 30	> 70	> 100
		> 150	> 200	> 250
		> 300	> 400	
TOLERANCE UNLESS OTHERWISE SPECIFIED				
[±0.15] [±0.2] [±0.3] [±0.4] [±0.5] [±0.6] [±0.8] [±1] [±1.2]				
ANGULAR TOLERANCE ±2°				

(2) PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

PART DRAWING	
STYLE	
VOLUME (QNP)	DISTR CODE
SEE CHART	D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2001 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REBAROLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	NX

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH	
DR B. NAGY	DATE 27JN96
APVD1 M. MCCALL	16JL97
APVD2 M. MCCALL	16JL97
APVD3 M. CHUPAK	25JL97
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL POLYPROPYLENE COMPOUND PURPLE	
DRAWING NAME TAXI LOCK PLR GT	
DRAWING NUMBER 15326964	
SIZE A1	SCALE 5:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV 07

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15326810](#) [13511996](#)