



## HES240 Male Inline 5mm<sup>2</sup> ISO cable



### BENEFITS

- Inner connector with TPA can be plugged into header during device assembly (on wire-to-device)
- Industry-leading vibration and sealing performance
- Field proven design used across electrification market



### FEATURES

- Tool-less unmating system
- Finger proof/touch safe
- Aluminum compression bushings
- ISO cable compatible



### AVAILABLE CONFIGURATIONS

Connector Type	Wire-to-device, wire-to-wire
Cable Exit Orientation	90°, 180°
Cable Range (mm <sup>2</sup> )	2 - 5 (power) 0.5 (HVIL)
Terminal Type	CTS 2.8, Metri-pack 2.8
# of Power Terminals	2
Shielding Type	Individual
HVIL	Shunt on female
Assembly Assurance	CPA/TPA
Number of Indexes	3 (180°), 1 (90°)




### BILL OF MATERIALS

**HES240 Male Inline, 5mm<sup>2</sup> ISO cable**  
Kit part number: 35605967 contains:

Part Number	Description	Quantity
13990588	Male Inline Connector	1
13663724	1.0 HES gold-plated 0.75–1.0 mm <sup>2</sup>	2
13783284	2.4 HES gold-plated 4–5 mm <sup>2</sup>	4



## PERFORMANCE



## ASSOCIATED PARTS


### HES240 Female Connector, 5mm<sup>2</sup> ISO cable

Kit part number: 35602261 contains:

Part Number	Description	Quantity
13879046	Mating Connector	1
13663728	1.0 HES gold-plated 0.75–1.0 mm <sup>2</sup>	2
13783301	2.4 HES gold-plated 4–5 mm <sup>2</sup>	4



## DIMENSION MEASUREMENT SAMPLE



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)  
[35605967](#)