


DELPHI
D - 62119 WERMENTAL

SICHTVERMERKE:

	Y	N
SECONDARY LOCK ZWEITVERRIEGELT	X	
WATERPROOF WASSERDICHT		X

MATING PART : SEE CHART/SIEHE TABELLE
GEGENSTUECK
INSCRIPTION : 0.2 MM RAISED/ERHABEN
BESCHRIFTUNG

<input type="checkbox"/> DIM TO CHECK PRUEFMASSE	$\pm 0.2 \text{ MM}$	DIMENSIONAL TOLERANCE (MM) DIMENSIONSTOLERANZ (MM)																												
<input checked="" type="checkbox"/> DIM FOR HELP HILFSMASSE	$\pm 0.1 \text{ MM}$	<table border="1"> <tr> <td>FROM</td> <td>0</td> <td>20</td> <td>> 20</td> <td>> 30</td> <td>> 40</td> <td>> 50</td> <td>> 60</td> <td>> 70</td> <td>> 80</td> <td>> 90</td> <td>> 100</td> <td>> 150</td> <td>> 200</td> </tr> <tr> <td>TOLERANCE</td> <td>0</td> <td>0.05</td> <td>0.10</td> <td>0.15</td> <td>0.20</td> <td>0.25</td> <td>0.30</td> <td>0.35</td> <td>0.40</td> <td>0.45</td> <td>0.50</td> <td>0.60</td> <td>0.70</td> </tr> </table>	FROM	0	20	> 20	> 30	> 40	> 50	> 60	> 70	> 80	> 90	> 100	> 150	> 200	TOLERANCE	0	0.05	0.10	0.15	0.20	0.25	0.30	0.35	0.40	0.45	0.50	0.60	0.70
FROM	0	20	> 20	> 30	> 40	> 50	> 60	> 70	> 80	> 90	> 100	> 150	> 200																	
TOLERANCE	0	0.05	0.10	0.15	0.20	0.25	0.30	0.35	0.40	0.45	0.50	0.60	0.70																	
<input type="checkbox"/> THEORETIC DIM THEORET. MASSE		TOLERANCE UNLESS OTHERWISE SPECIFIED TOLERANZ UNLESS OTHERWISE SPECIFIED ANGULAR TOLERANCE IN ° WINKELTOLERANZ IN °																												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15426894](#)