



DO NOT SCALE

THIS DRAWING AND DESIGN HEREON CONSTITUTE A PROPRIETARY DESIGN OF PACKARD ELECTRIC DIVISION AND IS NOT TO BE DUPLICATED OR REPRODUCED WITHOUT AUTHORITY OF PACKARD ELECTRIC DIVISION.



SEALING RIBS MUST BE FREE OF DEFECTS






STANDARD CONSTRUCTION

OPTIONAL CONSTRUCTION

CABLE END VIEW OF CONN. BODY

6.15 DIA. - 6 PLCS.



- NOTES** —
1. USE FEMALE TERMINAL 12034051 OR EQUIVALENT FOR "IN-LINE" APPLICATIONS. USE MALE TERMINAL 12033674 OR EQUIVALENT FOR "PANEL MOUNT" APPLICATIONS.
 2. USE CABLE SEAL 12015323 OR EQUIVALENT.
 3. MATING CONNECTOR - DELCO ELECTRONIC PART #16008965 OR EQUIVALENT.
 4. WHEN PARTS ARE SHIPPED, THEY MUST BE PACKED IN PLASTIC BAGS OR SHIPPING CONTAINERS MUST BE LINED WITH PLASTIC LINERS. BAGS OR LINERS MUST BE SEALED TO AVOID ENTRY OF FOREIGN MATTER.
 5. SEALING CODE 3.

DATE	SYM.	REVISION RECORD	AUTH	DR.	CK.
05MY80	A	RELEASED	80005	JH	JH
09FE81	-	ADDED STANDARD & OPTIONAL CONST. VIEWS	75211	DB	JK
21JA82	-	38.50 ± .20 DIM WAS 38.50 ± .15	79596	DB	JK
19JL83	-	1.5 MAX. WAS 1.0 MAX.	85923	FW	JK
11SE87	-	REVISED NOTE #1 & ADDED NOTE #5	115623	TB	JK
21OC87	-	REVISED TERMINAL NOTE	116529	JH	JK

PART NO.
1201 5199

METRIC

DIMENSIONS ARE IN MILLIMETRES
UNLESS OTHERWISE SPECIFIED

P. N. C. CODE	
CODE NO. 6900	TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: ANGULAR ± 2° TWO PLACE ± 0.15 ONE PLACE ± 0.5
QC-C-5110	
DWG. DATE 05MY80	SCALE NONE
EST. NO.	DATE 06MY80
REFERENCE NO.	DATE 07MY80
MATERIAL SPEC. SEE DWG.	
NAME ASM CONN 6M/E W/P TWR	
PART NO. 1201 5199	SIZE C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12015799](#) [12015799-B](#)