

Component-to-wire connectors


Sicma



2 way female housings for 2.8 mm terminals

Features

- High density, reduced size housings
- Hinge secondary lock for terminal position assurance (T.P.A.)
- 2 way housing compatible with ISO standard for loudspeaker
- Several colour codings available



Performance characteristics

- Temperature range:
from -40°C to +125°C
- Contact retention force: > 120 N
- Contact insertion force: < 7 N
- Connector mating force: < 30 N

Construction

- Housing material: PBT

Tooling

- Terminal removal tool: 210S045
- Flap opening: 210S043

Connector compatibility

- Usable terminals:
 - Sicma-2 2.8 mm female terminals
 - Sicma-3 2.8 mm female terminals

Part Numbers	No. of position	Terminal size	Colour
211 PC023S0017	2	2.8 mm	Black
211 PC023S6017	2	2.8 mm	Blue
211 PC023S8017	2	2.8 mm	Grey
211 PC023S9017	2	2.8 mm	Crystal

Component-to-wire connectors


Sicma

FCi


2 way female housings for 2.8 mm terminals

Dimensional characteristics

Notes:



Codings



Brochures & catalogs
Product documentation
Technical library

€ Price request

Application	Wire to Device
Ways	2
Coding version	Blue
Product Type	Housing
Coding	Yes
Family	Wire to Device
Features	High Density, Reduce Size Housing Compatible ISO Standard for Loudspeaker

	Hinge Secondary Lock for Terminal Position Assurance (T.P.A.)
Hybrid	No
Main Terminal family	Sicma
Main Terminal size	2.8 mm
Sealed	No
Terminal Size	2.8
Mechanical	
Connector mating force	< 30N
Physical	
Color	Blue
Material	PBT
Temperature (Range)	-40°C to+125°C
Terminal 1 Type	
Terminal type 1	Sicma Female 2.8 mm Terminal
Ways for Terminal Type 1	2
Contact insertion force for Terminal Type 1	< 7N
Retention force (Contact) for Terminal Type 1	> 120N
Environmental	
IMDS	Yes
Other Features	
Type	Female
Disclaimer	For more Information, please contact your local sales office. Displayed data is for information purposes only. The supply of some products might be limited to some customers.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[211PC023S9017](#) [211PC023S8017](#)