

Direct Link

Cross reference

RoHS/LF P/N Search

Customer drawing search

3D model search

Application tooling

Services

Contact us

Distributor list

Price request

Order samples

Documentation


Free search

Search by category

Start > Search=240PC023S0117* > 240PC023S0117

240PC023S0117

240PC023S0117 : 2 Way 2.8 mm injector and pressure sensor



Customer Drawing

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Specifications

General

Mechanical

Physical

Terminal 1 Type

Environmental

Other Features

General

Application	Engine Compartment Connectors Component to Wire Injector-Sensor
Ways	2
Coding version	Black
Product Type	Housing
Coding	Yes
Features	Suitable for all High Pressure Injector Systems 2 W Female Injector Connector High Vibration Design by Compressed interfacial Seal Suitable for Common Rail
Hybrid	No
Main Terminal family	DCS-2
Main Terminal size	2.8 mm
Sealed	Yes
Terminal Size	2.8

Mechanical

Connector mating force	< 60 N
------------------------	--------

Physical

Color	Black
Material	PBT
Temperature (Range)	-40 °C to +125 °C

Terminal 1 Type

Terminal type 1	DCS-2 Female 2.8 mm Terminal
Ways for Terminal Type 1	2
Contact insertion force for Terminal Type 1	< 15 N
Contact Pitch for Terminal Type 1	5 mm
Retention force (Contact) for Terminal Type 1	> 100N

Environmental

IMDS	Yes
------	-----

Other Features

Market	Passenger Vehicles
Type	Female
Part Situation	Active

Disclaimer

Displayed data is for information purposes only.
For more information, please contact your local sales office.
The supply of some products might be limited to some customers.

http://portal.fciconnect.com/Comergent/en/US/adirect/fci?cmd=catProductDetail&showAddButton=true&productID=240PC023S0117&_... 6/26/2009

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[240PC023S0117](#)