

Direct Link

Cross reference

RoHS/LF P/N Search

Customer drawing search

3D model search

Application tooling

Services

Contact us

Distributor list

Price request

Order samples

Documentation


Free search

Search by category

Start > Search=60400551* > 60400551

60400551

60400551 : 7 Way Component-to-Wire Female housing



Customer Drawing

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Specifications

General	Mechanical	Physical	Terminal 1 Type	Environmental	Other Features
General					
Application			Engine Compartment Connectors Component to Wire		
Ways			7		
Product Type			Housing		
Coding			No		
Features			Mechanical Polarization Sealing Protection IP 67 Metal Locking Feature Flat Interface Seal Additional Terminal Locking Device Pre - Assembled on Front Part of the Housing Acceptable Wire Range from 0.35 to 1.5 mm²		
Hybrid			No		
Main Terminal family			DCS-1		
Main Terminal size			2.8 mm		
Sealed			Yes		
Terminal Size			2.8		
Mechanical					
Connector mating force			< 90 N		
Physical					
Color			Black		
Material			PBT		
Temperature (Range)			-40 °C to +120 °C		
Terminal 1 Type					
Terminal type 1			DCS-1 Female 2.8 mm Terminal DCS-1 Power Female 2.8 mm Terminal		
Ways for Terminal Type 1			7		
Contact insertion force for Terminal Type 1			< 20 N		
Contact Pitch for Terminal Type 1			5 mm		
Retention force (Contact) for Terminal Type 1			> 80N		
Environmental					
IMDS			Yes		
Other Features					
Market			Passenger Vehicles		
Type			Female		
Part Situation			Active		
Disclaimer			Displayed data is for information purposes only. For more information, please contact your local sales office. The supply of some products might be limited to some customers.		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[60400551](#)