

Specifications	
<div><div></div><div>General</div><div></div><div>General</div></div>	<div>General</div> <div>Mechanical</div> <div>Physical</div> <div>Terminal 1 Type</div> <div>Environmental</div> <div>Other Features</div>
Application	Component to Wire Injector-Sensor Engine Compartment Connectors
Ways	2
Coding version	Black
Product Type	Housing
Coding	Yes
Features	Accepting cable or wire guiding cap mountable by simple snap-on Suitable for all High Pressure Injector Systems 2 W Female Injector Connector High Vibration Design by Compressed interfacial Seal Suitable for Common Rail
Hybrid	No
Main Terminal family	DCS-2
Main Terminal size	2.8 mm
Sealed	Yes
Terminal Size	2.8
Mechanical	
Connector mating force	< 60 N
Physical	
Color	Black
Material	PBT
Temperature (Range)	-40 °C to +125 °C
Terminal 1 Type	
Terminal type 1	DCS-2 Female 2.8 mm Terminal
Ways for Terminal Type 1	2
Contact insertion force for Terminal Type 1	< 15 N
Contact Pitch for Terminal Type 1	5 mm
Retention force (Contact) for Terminal Type 1	> 100N
Environmental	
IMDS	Yes
Other Features	
Market	Passenger Vehicles
Type	Female
Part Situation	Active
Disclaimer	Displayed data is for information purposes only. For more information, please contact your local sales office. The supply of some products might be limited to some customers.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[F232200](#)