










TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 101



RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO

RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 12089660
MAX. INSULATION CRIMP MUST BE LESS THAN 2.3 HIGH AND 3.5 WIDE
MAX CABLE O.D. 2.4 REFER TO ESA-605 FOR CRIMP DIMENSIONS
CONNECTOR POSITION ASSURANCE LOCK 12064989
TERMINAL POSITION ASSURANCE LOCK 12064986
- FOR POLYESTER IN-PROCESS MOISTURE AND PART DEGRADATION LIMITS, SEE ESO-1502

SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	21	NO MISSING SYMBOL NUMBER
	LAST NO. USED	20	

DWG STATUS				ZONE		REVISION HISTORY		AUTH		DR		AP/D	
DATE	STG	REV	N/P	CHG									
03A099	R	01	-	-			CLEARED REV COLUMN & 15356878 - RELEASED	990005	JHN	JVM	RJ		
070C99	R	02	-	-			ALL PARTS - REV TOL (B PLCS)	197614	TLP	TLP	RJ		
29A000	R	03	-	-			ALL PARTS - ADDED MAT'L TO R1B5	202902	JVD	EAR	90		
030C01	R	04	-	-			ALL PARTS - ADDED OPT CONSTRUCTION & MATERIAL RECYCLING CODE NOTES	213743	HH	EDV	90		
23A006	R	05	-	-			ALL PARTS - REVISED REVISION LEVEL DUE TOOLING REVISION LEVEL AND UPDATED MAT'L SPEC	276494	EPS	FKV	MGR		

PART NO	REV	N/P	STATUS	TYPE	MATERIAL SPECIFICATION AND COLOR	MATING CONNECTOR	VOL cm ³	USE TMC
15356878	01	AA		101	M4695007 PBT-GRN	12040905	2.544	-
12066130	B	1		102	M4695001 PBT NAT	12047813	2.540	*
12065672	B	1		103	M4695003 PBT GRA	12065671	2.540	-
12064980	B	1		101	M4695002 PBT BLK	12040905	2.544	-

ECT No.	REVISION RECORD	WEIGHT	WEIGHT TOL
081W1954	NEW ADOPTION	13.24	±0.15g
TOYOTA PART NAME		TOYOTA PART No.	
HOUSING CONNECTOR FEMALE		90080-98185	
APPROVED		CHECKED	
STAFF CODE DM700		TOYOTA MOTOR CORPORATION	

DIMENSIONAL RANGE (MM)		CHART	
FROM	TO	> 0	> 300
0	20	20	300
20	30	30	300
30	70	70	300
70	100	100	300
100	150	150	300
150	200	200	300
200	250	250	300
250	300	300	300
300	400	400	300

THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA		USE MATH DATA	

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
AP/D1 H. CASTRILLON	24N097
AP/D2 JOSE HUERTA	02DE97
AP/D3	
AP/D4	
AP/D5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHART	
DRAWING NAME	
TAXI CONN F MIC/P 100	
DRAWING NUMBER	
12064979	
SIZE A0	SCALE 5:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG REV N/P	R 05

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12064980](#)