





SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	9
	LAST NO. USED	8

MISSING SYMBOLS		DWG STATUS				ZONE	REVISION HISTORY		AUTH	DR	APVD 1	APVD 2
		DATE	STG	REV	N/P							
NO MISSING SYMBOL NUMBER		12N003	R	01	-	-		ALL ACTIVE PARTS - REDRAWN TO PD AND REVISED GRAPHICS	247796	LOA	FKV	RD
		17MR04	R	02	-	-		12033979 - REVISED CHART TO CORRECT REVISION LEVEL	252842	ADK	ADK	ET
		29N006	R	03	-	-		ALL ACTIVE PARTS - ADDED TYPE 101 & 102	287336	SGM	SGM	MO



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE DIE
SERIES NUMBER (P01, P02, P03, ETC).

				.018X1.500		12033980	A2	-		M1573068	102	0.8-0.5	3.13-2.03	19	X	-	.125	.195
				.018X1.500		12033979	A2	-		M1573068	102	0.8-0.5	3.13-2.03	19	-	X	.125	.195
12033977	A		OBSOLETE	.018X1.500	M1403068	12033978	A2	-		M1573068	102	0.8-0.5	3.13-2.03	19	X	X	.125	.195
				.018X1.500		12015685	D	-	OBSOLETE	M1573068	101	0.8-0.5	3.13-2.69	19	X	-	.135	.185
				.018X1.500		06288815	AH	2		M1573068	101	TWO 0.8-0.5	2.40-2.03	2.19	-	X	.190	.250
				.018X1.500		06288814	AJ	-	OBSOLETE	M1573068	101	0.8-0.5	2.40-2.03	19	-	X	.135	.175
				.018X1.500		06288811	AG	-	OBSOLETE	M1573068	101	TWO 2.0-1.0	3.97-3.36	2.15	-	X	.230	.385
				.018X1.500		06288810	AG	2		M1573068	101	TWO 2.0-1.0	3.05-2.48	2.15	-	X	.230	.305
				.018X1.500		06288809	AH	2		M1573068	101	2.0-1.0	3.97-3.36	15	-	X	.155	.230
				.018X1.500		06288808	AH	2		M1573068	101	2.0-1.0	3.05-2.48	15	-	X	.155	.185
				.018X1.500		06288785	AH	-	OBSOLETE	M1573068	101	0.8-0.5	3.13-2.69	19	X	X	.135	.185
02984149	AG		OBSOLETE	.018X1.500	M1403068	02984008	AG	2		M1573068	101	TWO 2.0-1.0	3.97-3.36	2.15	X	X	.230	.385
02984148	AH		OBSOLETE	.018X1.500	M1403068	02977448	AH	2		M1573068	101	2.0-1.0	3.97-3.36	15	X	X	.155	.230
02973105	AH		OBSOLETE	.018X1.500	M1403068	02973216	AH	2		M1573068	101	2.0-1.0	3.05-2.48	15	X	X	.155	.185
02973104	AG		OBSOLETE	.018X1.500	M1403068	02973215	AG	2		M1573068	101	TWO 2.0-1.0	3.05-2.48	2.15	X	X	.230	.305
02973236	AJ		OBSOLETE	.018X1.500	M1403068	02965805	AJ	-	OBSOLETE	M1573068	101	0.8-0.5	2.4-2.03	19	X	X	.135	.175
02973235	AH		OBSOLETE	.018X1.500	M1403068	02965806	AH	2		M1573068	101	TWO 0.8-0.5	2.4-2.03	2.19	X	X	.190	.250
PART	NO	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC	PART	NO	REV	N/P	STATUS	MAT'L SPEC	TYPE	SIZE (MM²)	DIA (MM)	ID	NIB	TANG
UNPLATED							TIN PLATED					CABLE			FEATURES			
																E±.015		
																F±.015		

6 PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (IN)	CHART J
FROM 0	>.500
TO .500	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±.005	±.010
ANGULAR TOLERANCE ±2°	

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (DN)	DISTR CODE	D	
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 3M GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE DIMED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN INCHES			
REFERENCE			
THIRD ANGLE PROJECTION	DO NOT SCALE	UNIGRAPHICS	
USE MATH DATA			

DELPHI						
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH						
DR	DATE					
APVD1 LUIS ORDUNA A.	12N003					
APVD2 FCO. W. KOPCA	14N003					
APVD3 RICHARD DICINTIO	26N003					
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001						
MATERIAL SEE CHART						
DRAWING NAME TAXI TERM F 59 SERIES						
DRAWING NUMBER 02962867						
SIZE A1	SCALE 5:1	FRAME NO 1 OF 1	SHEET NO 1 OF 3	STG R	REV 03	N/P -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[02973216](#) [02973215](#) [02977448](#) [06288808](#) [12033979](#)