


NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. MATERIAL RECYCLING CODE PER ISO 11469. (.091)X(.004) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
3. REFERENCE MATING COMPONENTS OR EQUIVALENT:

TERMINAL 02962572
4. (.091)X(.004) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

08917881	H	OBsolete	M2097001 POLYP-COPOLYMER BLK
08911256	10		M3592024 PA66 HS IM CRM
PART NO	REV	N/P	STATUS MATERIAL SPECIFICATION AND COLOR

DWG TYPE		PART DRAWING				
STYLE						
VOLUME (CM ³)	DISTR CODE	DATE				
		DR JIM CRAWFORD				
		APVD1 TOM MUDDREY	10AP75			
		APVD2 J.S.HAROLDSON	11AP75			
		APVD3 R.PHILLIPS	14AP75			
		APVD4				
		APVD5				
B						
UNLESS OTHERWISE SPECIFIED						
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.						
ALL DIMENSIONS ARE IN INCHES						
REFERENCE						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001						
MATERIAL SEE CHART						
DRAWING NAME						
TAXI CONN F 56 SERIES						
DRAWING NUMBER						
A						
ED R 2° 5		THIRD ANGLE PROJECTION	DO NOT SCALE			
 		 	USE MATH DATA			
DRAWING NUMBER 08917882						
SIZE A0	SCALE NONE	FRAME NO 1 OF 1	SHEET NO 1 OF 1	STG R	REV 03	N/P -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[08911256](#)