



- SEALING RIBS MUST BE FREE OF DEFECTS.

6.15 DIA - 3 PLCS




INDEX CODE
-202-
ALSO SEE HANDBOOK



- 12010718 - SEAL

- CONN BODY - SEE CHART

- FLEX AREA MAY EXHIBIT MATERIAL SEPARATION AFTER FINAL ASSEMBLY



— TERMINAL LOCK TO BE FOLDED
DOWN AS SHOWN AFTER
TERMINALS HAVE BEEN
INSERTED.

22.5
REF

20.8
REF



- 1.5 MAX GAP ALLOWABLE

- 40.5 REF

- ASM DIMENSIONING POINT

NOTES:

1. USE MALE TERMINAL ONLY, 12089040 OR EQUIVALENT.
2. USE CABLE SEAL 12015323 OR EQUIVALENT.
3. MATING PART - DEVICE
4. WHEN PARTS ARE SHIPPED, THEY MUST BE PACKED IN PLASTIC BAGS OR SHIPPING CONTAINERS MUST BE LINED WITH PLASTIC LINERS. BAGS OR LINERS MUST BE SEALED TO AVOID ENTRY OF FOREIGN MATTER.
5. SEALING CODE 3.
6. WHEN DESIGNING A PART TO MATE TO THIS WEATHER PACK CONNECTOR, REQUEST THE LATEST COPY OF DRAWING NUMBER 12020084 FROM THE PACKARD ELECTRIC DIVISION.
7. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSION)

STANDARD
CONSTRUCTION

OPTIONAL CONSTRUCTION




CABLE END VIEW OF CONN BODY

12103451	A		12103449	DEVICE	12089040/MALE	DEVICE
12020403	A		12020194	DEVICE	12089040/MALE	DEVICE
PART NO	REV	STATUS	CONN BODY	APPLICATION	REF: TERMINAL/GENDER	MATING PART

[illegible]

PART NO

1210 3452

			
THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED	
		TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: ANGULAR: $\pm 2^\circ$	
CODE NO	QC	ONE PLACE ± 0.3	
6900	-C-5110	TWO PLACE ± 0.15	
DWG DATE		DES	
17MY90		DR STEVE MARZO 17MY90	
SCALE		CK STEVE MARZO 21MY90	
2:1		APPR	
REFERENCE NO		A.R. HERMANN 24MY90	
12103450 "A0" SIZE		VOL CM ³	
MATERIAL SPEC			
SEE DRAWING			
NAME			
ASM CONN 3M W/P TWR			
PART NUMBER			SIZE
1210 3452			A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12103451](#) [12020403](#) [12020403-B](#)