







TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN
SCALE 2:1




TYPE 103
SAME AS TYPE 10
EXCEPT AS SHOWN
SCALE 2:1




TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN
SCALE 2:1





TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN
SCALE 2:1




CAVITY I.D. FOR TYPE 102 AND 105
CAVITY I.D. FOR TYPE 104 IS C16, C1, AND D16, D1
SCALE 2:1



CAVITY I.D. FOR TYPE 10
SCALE 2:1



TYPE 101



- ESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- ERIAL RECYCLING CODE PER ISO 11469. (1)X(0.1) CHARACTERS
SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.

S PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:

CAVITIES A,C,E16 AND B,D,F1 TO ACCEPT 12089649 TERMINAL.
MAX INSULATION CRIMP MUST BE LESS
THAN 3.55 HIGH AND 3.5 WIDE.

ALL CAVITIES TO ACCEPT 12089660 TERMINAL.
ALL OTHER CAVITIES MAX INSULATION CRIMP MUST BE LESS
THAN 2.3 HIGH AND 3.5 WIDE.

REFER TO ESA-605 FOR CRIMP DIMENSION
CAUTION: FOR GOLD INTERFACES CAVITIES A,C,E16 AND B,D,F1
TO ACCEPT 12103113 TERMINAL.

X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
PRIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY

IONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".

12110115	D5	-	-	M4698022 PBT-6F 30-BLU DK	105	8. 314	12129347	12129342	12129347	12129645	-	-
12110114	E4	-	-	M4698001 PBT-6F 30-TAN	104	8. 314	12129346	12129341	12129346	12129644	-	-
12110113	D5	-	-	M4698019 PBT-6F 30-RED DK	103	8. 314	12129345	12129340	12129345	12129643	-	-
12110112	A5	-	-	M4698029 PBT-6F 30-TAN	102	8. 314	12129367	12129369	-	-	-	-
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	TYPE	VOLUME	MATING CONNECTOR 32 WAY HEADERS TIN INTERFACE	MATING HEADER ASM	MATING CONNECTOR 32 WAY HEADERS GOLD INTERFACE	MATING HEADER ASM	MATING CONNECTOR 56 WAY HEADERS GOLD INTERFACE	MATING HEADER ASM

[illegible]

DELPHI
DELPHI PACKARD ELECTRIC SYSTEMS
WARREN, OH

			DATE
OR			
APV101	E. MONCISVAIS		22NO96
APV102	E. MONCISVAIS		22NO96
APV103	ENRIQUE BAEZ		22NO96

APYD4	
APYD5	

AND ATTENDS OF CLASS OF DATUM	SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001
-------------------------------------	---

	SEE CHART		
--	-----------	--	--

	DRAWING NAME	
--	--------------	--

	TAXI CONN F MIC/P 100	
--	-----------------------	--

DRAWING NUMBER 10110117 A

12110117

UNISUPPLICS	SIZE A1x3	SCALE 4:1	PLANE NO 1 OF 2	SHEET NO 1 OF 2	STD R	REV 04	NOT -
-------------	--------------	--------------	--------------------	--------------------	----------	-----------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12110113](#) [12110114](#)