










TYPE 102  
SAME AS TYPE 101  
EXCEPT AS SHOWN  
(OPTION B)



TYPE 103  
SAME AS TYPE 101  
EXCEPT AS SHOWN  
(OPTION C)







TYPE 104  
SAME AS TYPE 101  
EXCEPT AS SHOWN  
(OPTION D)





(2X 4)  
2X 17.55 ±0.1 TYP

SECTION A - A



TYPE 101  
(OPTION A)



SYMBOL DEFINITION  
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  
○ DOES NOT REQUIRE INSPECTION. IT MAY BE  
CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.

TOTAL NO OF  
INSPECTIONS  
REQUIRED  
7  
LAST NO.  
USED  
5

MISSING SYMBOLS  
NO MISSING SYMBOL  
NUMBER

| DATE   | STG | REV | N/P | CHG | ZONE | REVISION HISTORY                                                                  | AUTH   | DR  | AP/D | AP/D |
|--------|-----|-----|-----|-----|------|-----------------------------------------------------------------------------------|--------|-----|------|------|
| 12SE06 | R   | 01  | -   | -   | -    | ALL PARTS - RELEASED                                                              | 284643 | JR  | JR   | MP   |
| 10N006 | R   | 02  | -   | -   | -    | 13586137 REVISED GRAPHICS                                                         | 286776 | JR  | JR   | MP   |
| 29MR07 | R   | 03  | -   | -   | -    | ALL PARTS - REVISED GRAPHICS, PROCESS<br>SENSITIVE DIM #2 WAS #4 & ADDED CPA NOTE | 400995 | RJD | RJD  | MP   |

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:  
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND  
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION  
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL  
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL  
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) CHARACTERS  
AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:  
TERMINAL 13526678 & 13526680  
MAX INSULATION CRIMP MUST BE LESS  
THAN 3.1 HIGH AND 2.75 WIDE.
- FOR MATING CONFIGURATION REQUIREMENTS, SEE CHART.
- TERMINAL POSITION REQUIRES THE USE OF THE DELPHI BUILD/RING OUT  
HOLDER OR DELPHI NORTH AMERICA APPROVED EQUIVALENT. FAILURE TO  
DO SO CAN RESULT IN UNSEATED TERMINALS.
- (1)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY  
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.  
OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".
- PARTS NOT DESIGNED TO ACCEPT CPA

| PART     | NO | REV | N/P | MATERIAL SPECIFICATION AND COLOR | VOLUME | TYPE | OPTION | MATING CONNECTOR / EWCAP P/N |
|----------|----|-----|-----|----------------------------------|--------|------|--------|------------------------------|
| 13586137 | 02 | AA  |     | M4695007 PBT GRN                 | 3.621  | 104  | D      | 150-U-008-2-D01              |
| 13586136 | 01 | AA  |     | M4695027 PBT RST                 | 3.753  | 103  | C      | 150-U-008-2-C01              |
| 13586135 | 01 | AA  |     | M4695003 PBT GRA                 | 3.709  | 102  | B      | 150-U-008-2-B01              |
| 13586134 | 01 | AA  |     | M4695002 PBT BLK                 | 3.709  | 101  | A      | 150-U-008-2-A01              |

| FROM  | TO   | 0    | 20   | 30   | 70   | 100  | 150 | 200  | 250  | 300 | 400  |
|-------|------|------|------|------|------|------|-----|------|------|-----|------|
| 10.15 | ±0.2 | ±0.3 | ±0.4 | ±0.5 | ±0.6 | ±0.8 | ±1  | ±1.2 | ±1.5 | ±2  | ±2.5 |

| THIRD ANGLE<br>PROJECTION | DO NOT<br>SCALE | USE MATH<br>DATA |
|---------------------------|-----------------|------------------|
|                           |                 |                  |

**DELPHI**  
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE  
WARREN, OH

|                     |        |
|---------------------|--------|
| DR                  | DATE   |
| AP/D1 J. RICHARDSON | 12SE06 |
| AP/D2 J. RICHARDSON | 12SE06 |
| AP/D3 M. PENN       | 14SE06 |
| AP/D4               |        |
| AP/D5               |        |

SUBSTANCES OF CONCERN AND RECYCLED  
CONTENT PER DELPHI 10949001

MATERIAL  
SEE CHART

DRAWING NAME  
TAXI CONN F GT FBT 150

DRAWING NUMBER  
13520380

SIZE  
A0

SCALE  
3:1

FRAME NO  
1 OF 1

SHEET NO  
8 OF 11

STG REV N/P  
R 03 -

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)  
[13586134](#)