



SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	21	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	15		


DATE		STG	REV	N/P	CHG	ZONE	REVISION HISTORY		AUTH	DR	AP/D	AP/D
17MY06		R	01	-	-	-	CREATED PART DRAWING		280347	PR	PR	MDM
19JUL06		R	02	-	-	-	CAVITY ID NUMBERS ADDED		282785	PR	PR	MDM
09AUG06		R	03	-	-	-	REVISED LOCK AND ADDED PART NUMBERS		283225	PR	PR	MDM
12SEP06		R	04	-	-	-	ALL PARTS - REVISED SLOT AREA		284290	JS	JS	MDM




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN
(OPTION B)







TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN
(OPTION C)



TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN
(OPTION D)



TYPE 101
(OPTION A)



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (1.0)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 13526678 & 13526680
MAX INSULATION CRIMP MUST BE LESS THAN 3.1 HIGH AND 2.75 WIDE.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
SEE CHART
- (1.0)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED".
- CORRECT TERMINAL SEATING AND POSITION IN THIS CONNECTOR REQUIRES THE USE OF DELPHI DESIGNED BUILD FIXTURE/HOLDER P/N DP 13558697 OR EQUIVALENT. FAILURE TO DO SO CAN RESULT IN UNSEATED TERMINALS AND TERMINAL PUSH OUTS.
- SURFACE FINISH - MATTE FINISH EXCEPT WHERE OTHERWISE SPECIFIED.

13583667	02	-	M4695007 PBT GREEN	4.033	104	D	150-U-010-2-D01
13583666	02	-	M4695027 PBT BROWN	3.984	103	C	150-U-010-2-C01
13583665	02	-	M4695003 PBT GREY	3.997	102	B	150-U-010-2-B01
13583664	04	-	M4695002 PBT BLK	3.913	101	A	150-U-010-2-A01
PART NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	VOLUME	TYPE	OPTION	MATING CONNECTOR / EWCAP P/N

DIMENSIONAL RANGE (MM)		TOLERANCE	
FROM	TO	±	±
> 0	> 20	± 0.2	± 0.4
> 20	> 30	± 0.3	± 0.5
> 30	> 40	± 0.4	± 0.6
> 40	> 50	± 0.5	± 0.7
> 50	> 60	± 0.6	± 0.8
> 60	> 70	± 0.7	± 0.9
> 70	> 80	± 0.8	± 1.0
> 80	> 90	± 0.9	± 1.1
> 90	> 100	± 1.0	± 1.2
> 100	> 150	± 1.2	± 1.5
> 150	> 200	± 1.5	± 1.8
> 200	> 250	± 1.8	± 2.1
> 250	> 300	± 2.1	± 2.4
> 300	> 400	± 2.4	± 2.7
> 400	> 500	± 2.7	± 3.0
> 500	> 600	± 3.0	± 3.3
> 600	> 700	± 3.3	± 3.6
> 700	> 800	± 3.6	± 3.9
> 800	> 900	± 3.9	± 4.2
> 900	> 1000	± 4.2	± 4.5

THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
AP/D1 P. ROSA	17MY06
AP/D2 P. ROSA	17MY06
AP/D3 M.D. MCEOWEN	17MY06
AP/D4	
AP/D5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
DRAWING NAME	
TAXI CONN F FB 1.5	
DRAWING NUMBER	
13586672	
SIZE	SCALE
A0	2:1
FRAME NO	1 OF 1
SHEET NO	1 OF 1
STG	REV
R	04

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13583664](#) [13583665](#)