














TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN
(OPTION B)




TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN
(OPTION C)



TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN
(OPTION D)



TYPE 101
(OPTION A)



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
 - THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 13526678 & 13526680
MAX INSULATION CRIMP MUST BE LESS THAN 3.1 HIGH AND 2.75 WIDE.
 - FOR MATING CONFIGURATION REQUIREMENTS, SEE CHART.
 - TERMINAL POSITION REQUIRES THE USE OF THE DELPHI BUILD / RING-OUT HOLDER OR DELPHI NORTH AMERICA APPROVED EQUIVALENT. FAILURE TO DO SO MAY RESULT IN UNSEATED TERMINALS.
 - (1)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED" OR NO LOGO.
 - PARTS NOT DESIGNED TO ACCEPT CPA.

13592279	03	AB	M4695005 PBT GRN	3.174	101	A	150-U-006-2-A01	
13586133	03	AB	M4695007 PBT GRN	3.122	104	D	150-U-006-2-D01	
13586132	03	AB	M4695027 PBT RST	3.122	103	C	150-U-006-2-C01	
13586131	03	AB	M4695003 PBT GRA	3.174	102	B	150-U-006-2-B01	
13586130	03	AB	M4695002 PBT BLK	3.174	101	A	150-U-006-2-A01	
PART	NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	VOLUME	TYPE	OPTION	MATING CONNECTOR / EWCAP P/N

SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.			6-18	
TOTAL NO OF INSPECTIONS REQUIRED			7	
LAST NO. USED			18	

DWS STATUS				ZONE		REVISION HISTORY		AUTH		DR		AP/D	
DATE	STO	REV	N/P	CHG									
12JL06	R	01	-	-			ALL PARTS - RELEASED	281825	JR	JR	MP		
10AU06	R	02	-	-			ALL PARTS - ADDED NOTE #6 AND CALLOUTS IN VIEWS. 13586130-6131, AND 13592279 - REVISED GRAPHICS.	283482	JR	JR	MP		
30AU06	R	03					ALL PARTS - ADDED DELPHI LOGO & NOTE B, 13586132 - MATERIAL COLOR WAS BRN	284104	EES	EES	MP		
09OC06	R	04	-	-			REMOVED CALLOUTS (13 PLCS) & NOTE 7 AND REVISED ESD 53066202 AND NOTE 5	285330	EES	EES	MP		
16JA07	R	05	-	-			ALL PARTS - ADDED NOTE #7	400098	JEC	JEC	MP		
19AP07	R	06	-	-			ADDED "OR NO LOGO" TO NOTE #6	401116	OE	OE	MP		

DIMENSIONAL RANGE (MM)		TOLERANCE UNLESS OTHERWISE SPECIFIED		THIRD ANGLE PROJECTION		DO NOT SCALE	
FROM	TO	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6
0	20	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8
20	70	±0.3	±0.4	±0.5	±0.6	±0.8	±1.0
70	100	±0.4	±0.5	±0.6	±0.8	±1.0	±1.2
100	150	±0.5	±0.6	±0.8	±1.0	±1.2	±1.5
150	200	±0.6	±0.8	±1.0	±1.2	±1.5	±2.0
200	250	±0.8	±1.0	±1.2	±1.5	±2.0	±2.5
250	300	±1.0	±1.2	±1.5	±2.0	±2.5	±3.0
300	400	±1.2	±1.5	±2.0	±2.5	±3.0	±4.0

DELPHI
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
WYOMING, OH

DR	DATE
AP/D1 J. RICHARDSON	12JL06
AP/D2 J. RICHARDSON	12JL06
AP/D3 M. PENN	14JL06
AP/D4	
AP/D5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001

MATERIAL SEE CHART

DRAWING NAME
TAXI CONN F GT FBT 150

DRAWING NUMBER
13520380

SIZE A0
SCALE 3:1
FRAME NO 1 OF 1
SHEET NO 7 OF 11
STO REV N/P
R 06 -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13592279](#)