






DO NOT SCALE

137-A



- NOTES — 1. CAVITIES C16 AND D1 CAN ACCEPT TERMINAL 12089649 OR EQUIVALENT. ALL CAVITIF 5 CAN ACCEPT TERMINAL 12089660 OR EQUIVALENT.
2. CAVITIES C16 AND D1 CAN ACCEPT A MAX INSULATION CRIMP OF 3.55 HIGH AND 3.50 WIDE (3.55 MAX CABLE O.D.) ALL OTHER CAVITIES ACCEPT A MAX INSULATION CRIMP OF 2.30 HIGH AND 3.50 WIDE (2.40 MAX CABLE O.D.) REFER TO ESA-605 FOR CRIMP DIMENSIONS.
3. MATING INSULATOR 12059119, ASM 12059120 OR EQUIVALENT.
4. USE SECONDARY LOCK 12045389 AND 12045890 FOR STRAIGHT AND 12045889 AND 12048245 FOR RIGHT ANGLE OR EQUIVALENT.



As of 06 JUL 90, [redacted]
[redacted] maintained on [redacted] supervision.

C04D1954

PACKARD ELFO

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12059126](#)