






DO NOT SCALE


PART NO.
1206 6158

ART. NO. 1206 6158

[illegible]

NOTES

1. ALL RADII 0.40 UNLESS OTHERWISE SPECIFIED.
2. DIMENSIONS ARE TO FACE OF VIEW SHOWN, UNLESS OTHERWISE INDICATED.
3. 1" DRAFT ON ALL INSIDE AND OUTSIDE SURFACES. UNLESS OTHERWISE SPECIFIED.
4. LOCKING FEATURES ARE IDENTICAL EXCEPT AS SHOWN.
5. THIS PART MATES TO 12066156 CONN. BODY OR EQUIVALENT.
6. THIS PART IS NOT CONSTRUCTION FOR AUTOMATIC FEEDING.
7. MATERIAL RECYCLING CODE - "PP" PER SAE J1344. (2.3)(X)(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
8. (2.3)(X)(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

P . E . D . / <u>INTEGRAL</u>			
THIRD ANGLE PROJECTION			
6900		METRIC DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.	
CODE NO.		TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL	
0.C.-C-4004		ONE PLACE ± 0.3 TWO PLACE ± 0.15	
ANGULAR $\pm 2^\circ$			
DWG. DATE	27MY86	SCALE	4:1
EST. NO.		CK.	R. HERMOSILLO
REFERENCE NO.		APPR.	R. HERMOSILLO
		APPR.	E. TRACEY
MATERIAL SPEC.		DATE	05N002
		DATE	05N002
		DATE	06N002
M0661002 PP BLK			
NAME			
COVER CONN M/P			
PART NO.		SIZE	
1206		6158	
		D	

PACKARD ELECTRIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12066158](#)