








[illegible]

MOUNTING BRACKET

MATERIAL: SAE 1008 OR 1010
TOLERANCE: ONE PLACE ± 0.5
TWO PLACE ± 0.25

SCALE 4:1

NOTES


1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. DIMENSIONS MARKED "REF" ARE FOR REFERENCE ONLY
AND NO TOLERANCE LIMITS ARE ESTABLISHED.
3. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.

- 4. MATERIAL DISCOLORATION IS ACCEPTABLE IN THIS AREA (2 PLCS). DISCOLORATION DOES NOT IMPACT PRODUCT FIT OR FUNCTION.

PART NO
1216 3607

DRAWING TYPE PID		OTHER DRAWINGS AVAILABLE DETAIL	
			
THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED	
		TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: ANGULAR: ± 2°	
CODE NO	QC	ONE PLACE ± 0.3	
6901		TWO PLACE ± 0.15	
DWG DATE		DES	
10MR95		J. HOLMES 10MR95	
SCALE		DR	
2:1		RICARDO PINA 03MY95	
REFERENCE NO		CK	
		RICARDO PINA 03MY95	
		APPR	
		J.A. GOURASH 31MY95	
		VOL CM ³ 3.807	
MATERIAL SPEC			
R0071754 PA66 HS IM-BLK			
NAME			
CLIP IGN 7MM			
PART NUMBER			SIZE
1216 3607			A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12163607](#)