







- | | |
|--|--------------|
| <div> <div>23</div> <div>PROCESS SENSITIVE DIMENSION</div> </div> | |
| DIMENSIONS ENCLOSED IN () INDICATE
REFERENCE DIMENSIONS AND DO NOT TOLERANCE
LIMITS ARE ESTABLISHED | |
| DIMENSIONAL RANGE (MM) | CHART E-1 |
| FROM
TO | > 0
20 |
| > 20
30 | > 30
70 |
| > 70
100 | > 100
150 |
| > 150
200 | > 200
250 |
| > 250
300 | > 300
400 |
| TOLERANCE UNLESS OTHERWISE SPECIFIED | |
| ±0.15 | ±0.2 |
| ±0.3 | ±0.4 |
| ±0.5 | ±0.6 |
| ±0.8 | ±1 |
| ±1.2 | ±1.6 |
| ANGULAR TOLERANCE ±2° | |

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (QIP)	2.148	DISTR CODE	D
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994 AND AMENDED BY THE INC. COUNCIL ON STANDARDIZATION AND TOLERANCE DESIGNATION (CST), SEPARATE PATTERN OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION	DO NOT SCALE	USE MATH DATA	

 DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH									
OR								DATE	
APV01		E						18SE07	
APV02		J A N W		G U O				18SE07	
APV03		E						18SE07	
APV04									
APV05									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001									
MATERIAL M4695001 PBT NATURAL									
DRAWING NAME CONN 6 F BFC 180									
DRAWING NUMBER 1 3665466									
SIZE A0	SCALE 1:1	FRAME NO 1 OF 1	SHEET NO 1 OF 1	SHEET NO 1 OF 1	STO R	STO 01	REV A	REV AA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13665466](#)