











SCALE 2:1




SECTION C - C



SECTION A - A



SECTION B-B



- ## NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. SEALING CODE 0 - UNSEALED
3. MATERIAL RECYCLING CODE PER ISO 11469. (2,3)X(0,1) RAISED
CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
4. MATING COMPONENTS OR EQUIVALENT:
CAVITY A - MTA P/N 45-40310
CAVITY B - 15329073 OR 15425499
5. (2,3)X(0,1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.
6. DIMENSION TAKEN FROM CONNECTOR BASE

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	148
	LAST NO. USED	59

	MISSING SYMBOLS
g	NO MISSING SYMBOL NUMBER

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APPROV
DATE	STG	REV	N/P	CHG					
02AP02	R	01	-	-	WAS PE097534 AND RELEASED	222562	1HN	FR6	LP
23AP02	U	02	-	-	ADDED CUT-OUT WINDOW OP PCB SIDE OF CONNECTOR.	224251	JEB	JEB	LP
28MY02	R	03	-	-	THICKEN THIN FLOOR IN 2-WAY CAVITY: REVISED 60&T	225290	JR	JR	LP
05AU02	R	04	-	-	UPDATED PDM ATTRIBUTES	227237	MAC	MAC	LP
15OC02	R	04	AA	-	UPDATED PDM ATTRIBUTES	231506	LOA	FR6	LP
16MY03	R	05	-	-	UPDATED TO FIAT SPEC. 91320/4B ADDED MATING BOARD DETAIL	241286	SHH	SHH	LP
19AU03	R	05	AA	-	REVISED TOL ON DIM NO. 34 +0.25 / -0.1 WAS ±0.1	244929	SHH	SHH	LP
13NO03	R	05	AB	-	ADDED FLASH NOTE, DIM. NO. 59; REVISED PROCESS SENSITIVE DIMENSION	246892	SHH	SHH	LP
08AU06	R	05	AC	-	UPDATED DIM'S 7 PLCS WITH CORRESPONDING NOTE 6	283348	ABG	CJP	LP

		12 PROCESS SENSITIVE DIMENSION	
		DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)		CHART E1	
FROM	TO		
> 0	> 20	> 30	> 70
> 20	> 30	> 70	> 100
> 30	> 70	> 100	> 150
> 70	> 100	> 150	> 200
> 100	> 150	> 200	> 250
> 150	> 200	> 250	> 300
> 200	> 250	> 300	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.15	±0.2	±0.3	±0.4
±0.3	±0.4	±0.5	±0.6
±0.6	±0.8	±1	±1.2
ANGULAR TOLERANCE 42°			

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (Q/P)		DISTR CODE	
			
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994 AS AMENDED BY THE 2018 EDITION, TOLERANCES AND TOLERANCING ADOPTED IN 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUM ARE, BY RULE, UNLESS NOTED OTHERWISE, AND DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURE LOCATIONS IS DEFINED BY DIMENSION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE BASED SEPARATELY. ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
			
			
USE MATH DATA			

DELPHI DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH											
DR								DATE			
AP#01 ISRAEL HDEF NOV0A								02AP02			
AP#02 FCO. RESENDI								03AP02			
AP#03 LISA PROX								04AP02			
AP#04											
AP#05											
SUBSTANCES OF CONCERN AND RECYCLED CONTENT FOR DELPHI-A [1049001]											
MATERIAL MC 394002 PA6T/66 GF 33 HS BLK											
DRAWING NAME											
ASM CONN 12 M GT 150 M/P 800 COUPLING											
DRAWING NUMBER											
15424715											
SIZE		SCALE		FRAME NO		SHEET NO		STG		REV	
A4		2:1		1 OF 2		1 OF 1		R		05 AC	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15424715](#)