





SYMBOL DEFINITION		MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	5	
	LAST NO. USED	5	

DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD
DATE	STG	REV	N/P					
04AP00	R	001	-		ALL ACTIVE PARTS: REDRAWN TO PD., ADDED 66.24 ±2.11, NOTE & LABEL, REMOVED 18.6 MAX DIM & NOTE	198121	6EG	HH DN
04AP00	R	002	-		ALL ACTIVE PARTS-66.2 ±2 WAS 66.24 ±2.11 & REMOVED TYPE INFORMATION	199708	6EG	HH DN
25MY04	R	03	-		12066434 & 12077428 - RESTRICTED1 15492574 & 15492577 - RELEASED	255888	ESH	JAA MGR
180C05	R	04	-		12077428 - OBSOLETE	273276	JTV	AUG MGR
03AP06	R	05	-		12066434 - OBSOLETE AND ADDED REPLACED BY COLUMN	278753	CCV	JVM RMD



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- SEALING CODE 0 - UNSEALED
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- REFERENCE MATING COMPONENTS OR EQUIVALENT: CONNECTOR ASSEMBLY 12034257
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: CAVITIES A1, A6, B9 & F4 TO ACCEPT 12020125 TERMINAL OR EQUIVALENT. CAVITIES A2, A3, A7, A8, B1, B2, B6, B7, F1, F2, F6, F7, G1 & G6 TO ACCEPT 12020119 TERMINAL OR EQUIVALENT. ALL OTHER CAVITIES TO ACCEPT 12020116 TERMINAL OR EQUIVALENT. CONNECTOR TO ACCEPT 12048091 GREASE COVER, OR EQUIVALENT. SECONDARY LOCK 12034263
- THIS ASSEMBLY IS TO BE BOLTED TO MATING CONNECTOR ASSEMBLY WITH A TORQUE ON THE BOLT OF 5.6 NM TO 7.9 NM.
- DIMENSIONS INDICATED BY "■" ARE CONTROLLED FOR THE COMPONENT ASSEMBLY. ALL OTHER DIMENSIONS ARE CONTROLLED BY THE INDIVIDUAL COMPONENT DRAWING.



15492577	01	-	-	-	12066277	15492555	7MM HEX	1/4-20UNC-2A	15492512	0	-
15492574	01	-	-	-	12066277	15492516	1/4 INCH HEX	1/4-20UNC-2A	15492512	0	-
12089292	A	-	-	OBSOLETE	12045693	12059725	7MM HEX	1/4-20UNC-2A	12004737	0	-
12077428	A4	-	-	OBSOLETE	12066277	12059725	7MM HEX	1/4-20UNC-2A	12004737	0	-
12066434	A4	-	-	OBSOLETE	12066277	12015116	1/4 INCH HEX	1/4-20UNC-2A	12004737	0	15492574
12047693	B	-	-	OBSOLETE	12045693	12015116	1/4 INCH HEX	1/4-20UNC-2A	12004737	0	-
PART NO	REV	N/P	STATUS	CONNECTOR BODY	PART NO	HEAD SIZE	THREAD SIZE	RETAINER	SEALING CODE	REPLACED BY	

1	PROCESS SENSITIVE DIMENSION			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED				
DIMENSIONAL RANGE (MM)		CHART E		
FROM	0	> 20	> 30	> 70
TO	20	30	70	> 100
TOLERANCE UNLESS OTHERWISE SPECIFIED				
±0.15 ±0.2 ±0.3 ±0.4 ±0.5				
ANGULAR TOLERANCE 2°				

PART DRAWING	
STYLE	
VOLUME (10/1)	DISTR CODE
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE IN-SITU DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE NOTATIONS OF FEATURES MAY BE BASED SEPARATELY REBOLDED BY DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
APVD1 J. PARKER	27MR87
APVD2 J. COLDSNOW	30MR87
APVD3 O. J. GARCAR	09AP87
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
DRAWING NAME	
TAXI ASM CONN M M/P 280 480 630	
DRAWING NUMBER	
12077429	
SIZE	SCALE
A0	2:1
FRAME NO	1 OF 1
SHEET NO	1 OF 1
REV	R 05
N/P	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15492574](#)