




ITEM	QUANTITY	COMPONENTS DESCRIPTION	MATERIAL	COLOUR
1	1	24 WAY Female Housing	PBT GF15%	BLACK or GREY
2	1	TPA of DCS2 2.8 mm terminals	PBT GF30%	YELLOW
3	1	TPA of Duo Twin 0.64x0.64 terminals	PBT GF30%	YELLOW

NOTE:

A) Cavity suitable to mount the DCS2 2.8 mm female terminals
P/N 6 001 28 X1

B) Cavity suitable to mount the 0.64 mm Duo Twin female terminals
P/N 6 008 01 X1

C) The dimensions of 24 way male connector are showed
in the customer drawing FSC 309758

FEMALE CONNECTOR		HOUSING COLOUR	MALE CONNECTOR	
PART NUMBER			PART NUMBER	
1 721 24 00	13.25 ^{+0.20} ₀ 10.15 ⁰ _{-0.20}	BLACK	1 721 24 01	MVL
13725605	18.75 ^{+0.20} ₀ 15.65 ⁰ _{-0.20}		13725623	DELPHI
1 721 24 80	10.15 ⁰ _{-0.20} 13.25 ^{+0.20} ₀	GREY	1 721 24 81	MVL
13764398	18.75 ^{+0.20} ₀ 15.65 ⁰ _{-0.20}		13764407	DELPHI

14-07742	03-11-14	A		DELPHI P/N ADDED	S.N	F.G	M.C
57-06	05-09-06	03	-	Released for production			
ECN-NO. NUMERO -ECN	DATE DD/ MM / YY DATA	REVISION REVISIONE	POSITION POSIZIONE	CHANGE DESCRIPTION DESCRIZIONE MODIFICA	DRAWN BY DISEGNATORE	CHK. BY CONTROLLATO	APPR. BY APPROVATO
PRODUCT SPEC. SPEC. DI PRODOTTO	PACKAGING SPEC. SPEC. DI IMBALLAGGIO	APPLICATION SPEC. SPEC. DI APPLICAZIONE	COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.				
IPS 287	17212400 17212480	IPS 288 IPS 290	TOLERANCES TOLLERANZE ± 0.3 mm / ± 1° MATERIALE : See Table COLOUR : See Table TOOL NO. -				
DO NOT SCALE DRAWING DISEGNO FUORI SCALA		DATE DATA		NAME NOME		TITLE DESCRIZIONE	
DRAWN BY DISEGNATORE		31/01/04		G.Stella		24 WAY FEMALE CONNECTOR	
CHECKED BY CONTROLLATO		31/01/04		T.Ciriello		FSC 309757	
APPROVED BY APPROVATO						FILE NAME NOME FILE	
		ESR NO. NUMERO ESR		EU030781		CAT. NO. NUMERO CAT.	
				See Table		SCALE SCALA	
						2:1	

STRICTLY
CONFIDENTIAL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[17212480](#) [17212400-B](#) [17212480-B](#)