






ITEM	QUANTITY	COMPONENTS DESCRIPTION	MATERIAL	COLOUR
1	1	24 WAY Male Housing	PBT GF30%	BLACK or GREY
2	1	TPA of DCS2 2.8 mm terminals	PBT GF30%	YELLOW
3	1	TPA of Duo Twin 0.64x0.64 terminals	PBT GF30%	YELLOW
4	1	Lever	PA6.6 GF15%	RED



NOTE:

- A) Cavity suitable to mount the DCS2 2.8 mm male terminals P/N 6 011 06 X1
- B) Cavity suitable to mount the 0.64 mm male terminals.
- C) The dimensions of 24 way female connector are showed in the customer drawing FSC 309757
- D) Zone suitable to accept the fixing clip



14-07742	07/11/14	B		DELPHI P/N ADDED	S.N	F.G	M.C
12-00021	16/02/12	A		Modified Housing and Lever			
57-06	05-09-06	04	-	Released for production	G.B.	F.P.	M.C.
ECN-NO. NUMERO -ECN	DATE DD/ MM / YY DATA	REVISION REVISIONE	POSITION POSIZIONE	CHANGE DESCRIPTION DESCRIZIONE MODIFICA	DRAWN BY DISEGNATORE	CHK. BY CONTROLLATO	APPR. BY APPROVATO
PRODUCT SPEC. SPEC. DI PRODOTTO	PACKAGING SPEC. SPEC. DI IMBALLAGGIO	APPLICATION SPEC. SPEC. DI APPLICAZIONE	COPYRIGHT DELPHI CORPORATION AND/OR ITS THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.		AFFILIATES. ALL RIGHTS RESERVED. REVISED QUESTO DISEGNO E' PROPRIETA' DI DELPHI CORPORATION E CONTIENE INFORMAZIONI CONFIDENZIALI. LA RIPRODUZIONE, DISTRIBUZIONE E UTILIZZAZIONE DI QUESTO DOCUMENTO O DELLE SUE RELATIVE MATEMATICHE CAD, NONCHE LA COMUNICAZIONE DI QUALSIASI CONTENUTO AD ALTRI, SENZA ESPLICITA AUTORIZZAZIONE, E PROIBITA		
IPS287	17212401 17212481	IPS289 IPS290					
TOLERANCES TOLLERANZE		MATERIAL : MATERIALE :		SURFACE FINISH FINITURA SUPERFICIALE		CAD SYSTEM	
COUNTERPART Nr. CONTROPARTE Nr.		See Table		-		pro / eng.	
DO NOT SCALE DRAWING DISEGNO FUORI SCALA		TOOL NO.		LOC. CODE NAZIONALITA' IT		A3	
DATE DATA		NAME NOME		DRAWING NUMBER NUMERO DISEGNO		SHEET FOGLIO	
31/01/04		G.Stella		FSC 309758		1 of 1 di	
31/01/04		T.Ciriello				2	
APPROVED BY APPROVATO		ESR NO. NUMERO ESR		CAT. NO. NUMERO CAT.		SCALE	
		EU03781		See Table		2:1	

14-07742	07/11/14	B		DELPHI P/N ADDED	S.N	F.G	M.C
12-00021	16/02/12	A		Modified Housing and Lever			
57-06	05-09-06	04	-	Released for production	G.B.	F.P.	M.C.
ECN-NO. NUMERO - ECN	DATE DD / MM / YY DATA	REVISION REVISIONE	POSITION POSIZIONE	CHANGE DESCRIPTION DESCRIZIONE MODIFICA	DRAWN BY DISEGNATORE	CHK. BY CONTROLLATO	APPR. BY APPROVATO
PRODUCT SPEC. SPEC. DI PRODOTTO	PACKAGING SPEC. SPEC. DI IMBALLAGGIO	APPLICATION SPEC. SPEC. DI APPLICAZIONE	COPYRIGHT THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.	DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED QUESTO DISEGNO E' PROPRIETA' DI DELPHI CORPORATION E CONTIENE INFORMAZIONI CONFIDENZIALI. LA RIPRODUZIONE, DISTRIBUZIONE E UTILIZZAZIONE DI QUESTO DOCUMENTO O DELLE SUE RELATIVE MATEMATICHE CAD, NONCHE LA COMUNICAZIONE DI QUALSIASI CONTENUTO AD ALTRI, SENZA ESPLCITA AUTORIZZAZIONE, E PROIBITA			
IPS287	17212401 17212481	IPS289 IPS290					
TOLERANCES TOLLERANZE	+ 0.3 mm. / ± 1°	MATERIAL : MATERIALE :	SURFACE FINISH FINITURA SUPERFICIALE		DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE TORINO, ITALY		
COUNTERPART N°.r. CONTROPARTE N°.r.	17212400 17212480	COLOUR : COLORE :	-		CAD SYSTEM pro / eng.		
DO NOT SCALE DRAWING DISEGNO FUORI SCALA		TOOL NO.	LOC. CODE NAZIONALITA'		C ISO PROJECTION PROIEZIONE ISO		
DATE DATA	NAME NOME	TITLE DESCRIZIONE	DRAWING NUMBER NUMERO DISEGNO		DWG SIZE FORMATO A3		
DRAWN BY DISEGNATORE	31/01/04 G.Stella	24 WAY MALE CONNECTOR	FILE NAME NOME FILE		SHEET FOGLIO 2 of 1 di 2		
CHECKED BY CONTROLLATO	31/01/04 F.Ciriello		FSC 309758				
APPROVED BY APPROVATO			EUC03781		SCALE Scala 1:1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[17212481](#) [17212401-B](#) [17212481-B](#)