





STRICTLY
CONFIDENTIAL

LAY OUT 11 WAY



9.5mm FEMALE TERM. P/N F682210	8.0-10.0	60993304 YELLOW	10889241 YELLOW	5.4-6.6	60993306 WHITE	12186633 WHITE
9.5mm FEMALE TERM. P/N F582210	6.0	60993301 BLACK	15327788 BLACK	3.8-5.2		
9.5mm FEMALE TERM. P/N 60070451	4.0	60993308 GREEN	13546490 GREEN	3.4-3.7		
DCS2 2.8mm FEMALE TERM. P/N 60012941	1.5-2.5	60994034 YELLOW	10779161 YELLOW	2.7-2.9	60994007 GREEN	10779160 GREEN
DCS2 2.8mm FEMALE TERM. P/N 60012931	0.5-1.0	60994023 RED	10779159 RED	2.2-2.6		
DCS2 2.8mm FEMALE TERM. P/N 60012911	0.35	60994015 BLUE	10779162 BLUE	1.2-2.0		
USABLE TERMINAL FOR THIS CONNECTOR	WIRE SIZE	MVL P/N SWS COLOUR	DELPHI P/N SWS COLOUR	Ø INSULATION	MVL P/N CAVITY PLUG COLOUR	DELPHI P/N CAVITY PLUG COLOUR

ASSEMBLY CONFIGURATIONS

LAY OUT	9 WAY	7 WAY	10 WAY	11 WAY	
	 BLIND CAVITIES				
DELPHI P/N	13653766	33504496	33504497	13773530	
REV.	01	01	01	01	
MVL P/N	1721105	F554310	F654310	1721105A	
REV.	A	A	A	A	
CLOSED CAVITIES	5, 8	2, 3, 5, 8	9	none	
1 HOUSING	BLACK	DARK BROWN	DARK GREEN	GREY	PBT 30GF
2 SLIDE	RED	RED	RED	VIOLET	PA66 30GF
3 SEAL	RED	RED	RED	RED	SILICON RUBBER
REF. COMPONENT					MATERIAL

15-11342	30/01/15	F	-	DELPHI P/N ADDED	FG	-	MC
--	30/11/12	E	-	Correction dimension 013, 010 and general tolerance value	DT	-	MC
--	06/11/12	D	-	Correction on dimension 00land 010. New logo	DT	-	MC
12-01246	26/09/12	C	-	PN F682210 replaced 60070471 and F582210 replaced 60070461	DT	-	MC
12-00609	07/05/12	B	-	Added new layout 7way and 10way (ESR EU-120263) and layout 11way	DT	-	MC
			-	Modified cavities position of the 9way as the 11way (ref eca 12-01212)	DT	-	MC
12-00042	08/02/12	A	-	Changed Slide colour and drawing description	DT	-	MC
ECN-NO. NUMERO-ECN	DATE DD/ MM / YY	REVISION REVISIONE	POSITION POSIZIONE	CHANGE DESCRIPTION DESCRIZIONE MODIFICA	DRAWN BY CHK. BY APPR. DISEGNATORE CONTROLLATO APPROVA		
PRODUCT SPEC. SPEC. DI PRODOTTO	PACKAGING SPEC. SPEC. DI IMBALLAGGIO	APPLICATION SPEC. SPEC. DI APPLICAZIONE	COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.				
IPS 292	17211105	IPS 293	SURFACE FINISH FINITURA SUPERFICIALE				
TOLERANCES TOLLERANZE	± 0.3mm / ± 0.0125"	MATERIAL : MATERIALE :	SEE TABLE		DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE TORINO, ITALY		
COUNTERPART N°. CONTROPARTE N°.		COLOUR : COLORE :	SEE TABLE		C ISO PROJECTION PROIEZIONE ISO		
DO NOT SCALE DRAWING DISEGNO FUORI SCALA	TOOL NO. -	LOC. CODE NAZIONALITA' IT	D DIMENSION IN MILLIMETERS DIMENSIONI IN MILLIMETRI				
DRAWN BY DISEGNATORE	DATE DATA	NAME NOME	TITLE DESCRIZIONE		DRAWING NUMBER NUMERO DISEGNO		
CHECKED BY CONTROLLATO	30/07/04	R.P.	CONNECTOR FOR GLOW PLUG UNIT		FSD 309771		
APPROVED BY APPROVATO	30/07/04	T.C.	SEE TABLE		FILE NAME NOME FILE		
	30/07/04	T.C.	ESR NO. EU 120263		f3d309771		
			CAT. NO. NUMERO CAT.		SCALE SCALA		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[17211105-B](#)