









SECTION D-D
Schnitt D-D



SECTION C-C
Schnitt C-C



SECTION B-B
Schnitt B-B



DCS-2 1.3MM MALE
TERM.

DCS-2 1.5MM MALE TERM.	6 010 06 34	10751589	0.5-1.0	CONTACTBODY Grundfeder CuSn4 F47 Rm >470 N/mm²	SEL. 0.8µm Au MIN sel.0.8µm Au min
DCS-2 1.5MM MALE TERM.	6 010 06 14	10751586	022-0.35	LOCKING SPRING Ueberfeder X10CrNi18 8 ACC. DIN EN 10151	BLANK blank
USABLE TERMINALS FOR THIS CONNECTOR Geeignete Kontakte fuer diesen Stecker	MVL PART NO. MVL Teile Nr.	DELPHI PART NO. DELPHI Teile Nr.	WIRE SIZE Draht- groessen- bereich(mm²)	MATERIAL Material	SURFACE Oberflaeche

030	32	21
030	32	23

C	6 030 32 14	B	33500247	01	6 030 32 44	B	13795241	01	6 030 32 74	B	33511371	01	YELLOW/gelb	6 020 39 14	13795240
	6 030 32 18	B	33511366	01	6 030 32 48	B	33511368	01	6 030 32 78	B	33511372	01	GREY/grau	6 020 39 18	33500234
	6 030 32 21	B	33510865	01	6 030 32 51	B	33510873	01	6 030 32 81	B	33510881	01	BLACK/schwarz	T.B.D.	-
	6 030 32 23	B	33511367	01	6 030 32 53	B	33511369	01	6 030 32 83	B	33511373	01	RED/rot	6 020 39 23	33500235
	6 030 32 24	B	33510866	01	6 030 32 54	B	33510874	01	6 030 32 84	B	33510882	01	YELLOW/gelb	T.B.D.	-
	6 030 32 28	B	33510867	01	6 030 32 58	B	33510875	01	6 030 32 88	B	33510883	01	GREY/grau	T.B.D.	-

BENENNUNG		DRAWING NO.
4W UNSEALED MALE CONNECTOR		ZEICHN. -NUM.
IPS	PROJECT	

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[60303404](#) [60303234](#)