



MISSING SYMBOLS	DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APD	APD	1	2
	DATE	STG	REV	N/P	CHG								
NO MISSING SYMBOL NUMBER	04JAO7	R	04	-	-	ALL ACTIVE PARTS - CREATED PART DRAWING	400698	RMG	FRG				
	06JNO9	R	05	-	-	ALL ACTIVE PARTS - REDRAWN TO PD	404957	DJM	JVM	DGL			
	13AJO9	R	06	-	-	ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES	408647	DGM	GGI	MMR			
	20M113	R	07	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	410613	DGM	MMR				



- |   |   |   |
|---|---|---|
| END TYPE  | PART DRAWING  |   |
| TITLE   | <div style="display: flex; justify-content: space-between;"> <div>VOLUME (QM)</div> <div>DISTR CODE</div> </div> <div style="text-align: center; font-size: 2em; margin-top: 10px;">D</div> |   |
| UNLESS OTHERWISE SPECIFIED  |   |   |
| <p>THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994<br/>         AS AMENDED BY THE 2018 GLOBAL DIMENSIONING AND<br/>         TOLERANCING ADDENDUM-001. SEPARATE PATTERNS OF<br/>         FEATURES MUST BE SHOWN SEPARATELY FOR EACH OF DATUM<br/>         REFERENCES.</p> |   |   |
| ALL DIMENSIONS ARE IN INCHES  |   |   |
| REFERENCE   | 06294512  |   |
| THIRD<br>ANGLE<br>PROJECTION  | DO NOT<br>SCALE<br><br>USE<br>MATH  |   |
|   | NXX   |   |

<div>DELPHI</div> <div>DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH</div>											
DR							DATE				
AP#001 RICARDO MARTINEZ							04.JA.07				
AP#002 FCO. RESENDIZ							05.JA.07				
AP#003 DIANE L. SCHROCK							10.JA.07				
AP#04											
AP#05											
SUBSTANCES OF CONCERN AND RECYCLED CONTENT FROM DELPHI 10949001											
MATERIAL SHEET CHART											
DRAWING NAME											
TAXI TERM F P/C ED6BD-STD											
DRAWING NUMBER											
08917430											
SIZE A0		SCALE 1:0:1		FRAME NO 1 OF 1		SHEET NO 1 OF 1		STG R		REV 07	

A	B	12052213	B	OBSOLETE	.0160 X 1.438	METL NONFERROUS	C42500 EX HD	16	.089-.082	YES	103	.145
		12045052	B5		.0160 X 1.438	METL NONFERROUS	C42500 EX HD	18-20	.095-.081	YES	102	.125
		12020229	B	OBSOLETE	.0160 X 1.438	METL NONFERROUS	C42500 EX HD	TWO 22	.079-.053	YES	101	.140±.008
		12015044	B7		.0160 X 1.438	METL NONFERROUS	C42500 EX HD	12	.145-.139	YES	101	.180
		12010950	C6		.0160 X 1.438	METL NONFERROUS	C42500 EX HD	TWO 18-20	.095-.081	YES	101	.200
		12010767	C7		.0160 X 1.438	METL NONFERROUS	C42500 EX HD	22-24	.082-.044	YES	101	.085±.008
		12010533	B6		.0160 X 1.438	METL NONFERROUS	C42500 EX HD	14-16	.120-.101	YES	101	.145
		12010124	C	OBSOLETE	.0160 X 1.438	METL NONFERROUS	C42500 EX HD	18-20	.095-.081	YES	101	.125
		12004801	B6		.0160 X 1.438	METL NONFERROUS	C42500 EX HD	12	.145-.139	NO	101	.180
		12004460	C6		.0160 X 1.438	METL NONFERROUS	C42500 EX HD	TWO 18-20	.095-.081	NO	101	.200
		08917429	B6		.0160 X 1.438	METL NONFERROUS	C42500 EX HD	14-16	.120-.101	NO	101	.145
		08917271	B6		.0160 X 1.438	METL NONFERROUS	C42500 EX HD	18-20	.095-.081	NO	101	.125
		PART NO.	REV.	STATUS	MAT'L SIZE	MAT'L SPEC	SIZE (MM²)	DIA	DIMPLD CONTACTS	TYPE	E±.015	
		PLATED						CABLE				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12010533-L](#)