




THIS DRAWING AND DESIGN HEREON CON-
STITUTE A PROPRIETARY DESIGN OF
PACKARD ELECTRIC DIVISION AND IS NOT
TO BE DUPLICATED OR REPRODUCED WITH-
OUT AUTHORITY OF PACKARD ELECTRIC
DIVISION.

DO NOT SCALE

PART NO.
1200 4552
SHEET 2PART NO.
1200 4552
SHEET 2**TYPE 4**STRIP 7.0±1.4
DEDUCT 10.3**TYPE 5**STRIP 7.0±1.4
DEDUCT 10.3**TYPE 6**STRIP 7.0±1.4
DEDUCT 10.3

NOTE — CONTACT PACKARD ELECTRIC
SALES DEPARTMENT CONCERNING
CURRENT PRODUCT AVAILABILITY.

UNUSED CONDUCTOR WINGS (CRIMPED OR
UNCRIMPED) MUST NOT EXCEED 4.20
HEIGHT & 5.50 WIDTH.

UNUSED INSULATION WINGS (CRIMPED OR
UNCRIMPED) MUST NOT EXCEED 4.60
HEIGHT AND 5.90 WIDTH.

CABLE I.D. NUMBER (AS SPECIFIED IN
CHART) IS LOCATED ON UNDERSIDE OF
EACH TERMINAL.


MULTIPLE TERMINALS ARE MADE FROM
BASIC TERMINALS SPECIFIED IN CHART
BY TRIMMING AS SHOWN.

* POSITION OF CABLE IS OPTIONAL BETWEEN
LOCATIONS INDICATED.

* * INDICATES TERMINALS ARE MADE LOOSE AS
DUMMY TERMINALS NOT TO BE CRIMPED ON
CABLE. CONDUCTOR WINGS AND INSULATION
WINGS MAY OR MAY NOT BE CRIMPED.

■ INDICATES SERRATIONS IN CONDUCTOR
WINGS.

• INDICATES MATERIAL IS SILVER PLATED
OVER NICKLE PLATE.

**TYPE 7**

PART NO.	REV	STATUS	BASIC TERM	PART NO.	REV	STATUS	BASIC TERM	TYPE	SIZE (MM ²)	MAX DIA	ID NO.	A
12078148	A1	OBSOLETE	(4) 12078031						6 ■	—	—	11
12078147	A1	OBSOLETE	(3) 12078031						5 ■	—	—	11
12078146	A1	OBSOLETE	(2) 12078031						4 ■	—	—	11
12078144	A1	OBSOLETE	(4) 12078031						6 ■	5.0-3.0	5.10	11
12078143	A1	OBSOLETE	(3) 12078031						5 ■	5.0-3.0	5.10	11
12078142	A1	OBSOLETE	(2) 12078031						4 ■	5.0-3.0	5.10	11
				12078141	•	A1	OBSOLETE	(4) 12078136	6 ■	5.0-3.0	5.10	11
				12078140	•	A1	OBSOLETE	(3) 12078136	5 ■	5.0-3.0	5.10	11
				12078139	•	A1	OBSOLETE	(2) 12078136	4 ■	5.0-3.0	5.10	11
12066233	A1	OBSOLETE	(3) 12020337						5 ■	—	—	11
12065560	A1	OBSOLETE	(1) 12020334						** 7 ■	—	—	19
12052823	A1	OBSOLETE	(4) 12052443						6 ■	3.0	3.10	12
12052211	A1	OBSOLETE	(3) 12052443						5 ■	3.0	3.10	12
12052210	A1	OBSOLETE	(2) 12052443						4 ■	3.0	3.10	12
				12048292	•	A	OBS	(2) 12048293	4 ■	0.8-0.5	3.10	19
				12048288	•	A	OBS	(2) 12048289	4 ■	TWO 2.0-1.0	3.10	215
				12048287	•	A		(4) 12048291	6 ■	2.0-1.0	3.95	15
				12048286	•	A		(3) 12048291	5 ■	2.0-1.0	3.95	15
				12048285	•	A		(4) 12048290	6 ■	5.0-3.0	5.10	11
				12048284	•	A		(3) 12048290	5 ■	5.0-3.0	5.10	11
				12048283	•	A		(2) 12048291	4 ■	2.0-1.0	3.95	15
				12048282	•	A		(2) 12048290	4 ■	5.0-3.0	5.10	11
									** 6 ■	—	—	11
									6 ■	TWO 2.0-1.0	3.10	215
									5 ■	TWO 0.8-0.5	2.55	219
									6 ■	TWO 0.8-0.5	2.55	219
									4 ■	TWO 2.0-1.0	3.10	215
									** 4 ■	—	—	11
									6 ■	0.8-0.5	3.10	19
									6 ■	2.0-1.0	3.95	15
									5 ■	0.8-0.5	3.10	19
									5 ■	2.0-1.0	3.95	15
									6 ■	5.0-3.0	5.10	11
									5 ■	5.0-3.0	5.10	11
									4 ■	TWO 0.8-0.5	2.55	219
									4 ■	0.8-0.5	3.10	19
									4 ■	2.0-1.0	3.95	15
									4 ■	5.0-3.0	5.10	11
PART NO.	REV	STATUS	BASIC TERM	PART NO.	REV	STATUS	BASIC TERM	TYPE	SIZE (MM ²)	MAX DIA	ID NO.	A
			UNPLATED				PLATED					±0.4

12078160	A1	OBSOLETE	(4) 12078033						6 ■	3.0	3.10	12	4.6
12078159	A	OBSOLETE	(3) 12078033						5 ■	3.0	3.10	12	4.6
12078158	A1	OBSOLETE	(2) 12078033						4 ■	3.0	3.10	12	4.6
12078155	A3	OBSOLETE	(4) 12078032						6 ■	2.0-1.0	3.95	15	4.4
12078154	A3	OBSOLETE	(3) 12078032						5 ■	2.0-1.0	3.95	15	4.4
12078153	A3	OBSOLETE	(2) 12078032						4 ■	2.0-1.0	3.95	15	4.4
				12078152	•	A1	OBSOLETE	(4) 12078138	6 ■	2.0-1.0	3.95	15	4.4
				12078151	•	A1	OBSOLETE	(3) 12078138	5 ■	2.0-1.0	3.95	15	4.4
				12078150	•	A1	OBSOLETE	(2) 12078138	4 ■	2.0-1.0	3.95	15	4.4
PART NO.	REV	STATUS	BASIC TERM	PART NO.	REV	STATUS	BASIC TERM	TYPE	SIZE (MM ²)	MAX DIA	ID NO.	A	
UNPLATED				PLATED					CABLE	±0.4			

DATE	SYM	REVISION RECORD	AUTH	DR	CK
23JL84	—	ALL PARTS-REVISED & REDRAWN			
	—	—NO REV. UPDATE REQD.	91638	—	RLS
23JL84	—	12048282 THRU 12048288 & 12048292 ADDED & RELEASED			
	—	TO REV "A"	84005	—	RLS
14NO84	—	ADDED 12052210 & 12052211 & RELEASED TO REV. "A" & REPLOTED	84005	—	RFP FH
20JN85	—	12048288 & 12048292 MADE OBSOLETE & REPLOTED-REV. LEVEL REMAINS			
	—	THE SAME	85003	—	DKS TM
20JN85	—	12052823-OUTLINE DWG. ISSUED TO REV. "A"		—	DKS TM
02JL86	—	12065560 - RELEASED TO REV. "A".	860005	—	JP, DKS
02JL86	—	1204573, 12041233, & 12065560 - REVISED; NO REV. UPDATE REQD.	107390	—	JP, DKS
02OC86	—	12066233 - RELEASED TO REV. "A"	860005	—	JK JC
25NO86	—	12004565, 12004570, & 12004572 - BASIC TERMINAL WAS 12004560 - NO REV. UPDATE REQD			
	—	12004570 & 12004572-BASIC TERMINAL	110104	—	DY, DKS
10DE86	—	12004565 - REV. LEVEL "E" WAS "F"; 12004570 & 12004572 REV. LEVEL "F"			
	—	WAS "G" UNDER C/N 110104: 12004565, 12004570 & 12004572-BASIC TERMINAL			
	—	WAS 12066447-NO REV. UPDATE REQD	110800	—	DY, DKS
28JA86	—	REVISED " *" NOTE	111157	—	CDH FH
23SE88	—	12078139, 12078140, 12078141, 12078142, 12078143, 12078144, 12078146, 12078147, 12078148, 12078150, 12078151, 12078152, 12078153, 12078154, 12078155, 12078158, 12078159 & 12078160 - ADDED & RELEASED TO REV. "A"	880005	—	TJB H/L
25MR97	—	12078159 - OBSOLETE	960003	—	TM, TM
04FE04	—	12078153, 54, 55 - OBSOLETE	251516	—	BYP, BYP
24AU04	—	CORRECTED PREVIOUS DRAFTING ERRORS ON CN 251516	258153	—	BYP, BYP
09SE05	—	12078139-44, 12078146-48, 12078150-52, 12078158 & 12078160 - OBSOLETE	272096	—	CCV, FRG
08NO05	—	12010605 - WAS MADE OBSOLETE ON CNN 980003	274449	—	GPS, JAA
22AU08	—	12004564-67, 12004569, 12004570, 12004572, 12004573, 12004575, 12004823, 12004982, 12041233, 12052210-11, 12052823, 12065560, 12066233 - OBSOLETE	405838	—	JTZ, FKV
01SE08	—	12004573 & 12041233 - REINSTATED	405895	—	EAJ, FKV

CAD CAM (SHH)

METRIC		THIRD ANGLE PROJECTION	
DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED			
CODE NO.	6900,6901	TOLERANCE UNLESS OTHERWISE SPECIFIED	ANGULAR ± 2°
DWG DATE	07JN78	SCALE	DR.
CD X TERM	12004552.00.02	CK.	R. SEBRELL
REFERENCE NO.	*3 & *5	APPR.	DATE 03AU84
SHT	12004552 "D" SIZE	APPR.	R.D. KEARNS
MATERIAL SPEC.		DATE	04OC84
SEE CHART			
NAME			
TERM F PAC/ON III			
PART NO.			
1200 4552			
OUTLINE DRAWING			
SHEET 2			
PACKARD ELECTRIC			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12004571](#) [12004568-L](#) [12004571-L](#)