

DETAIL ALVEOLES 15
DETAIL CAVITIES 15


8 x 1.00 ± 0.05

0.20 ± 0.05

8 x 1.80 ± 0.05

0.20 ± 0.05

ECHELLE 5:1 / SCALE 5:1



DETAIL ALVEOLES 0.635
DETAIL CAVITIES 0.635

40 x 0.80 ± 0.05

40 x 0.90 ± 0.05


0.20

0.20

0.635

0.635

ECHELLE 5:1 / SCALE 5:1




Technical drawing of the right wiring out (SORTIE FAISCEAU A DROITE) showing a perspective view and a detailed dimensioned view.

Perspective View: Shows the lever assembly with a handle and a circular opening. The lever is labeled "N° D'EMPREINTE DU LEVIER" (LEVER CAVITY NUMBER).

Dimensioned View: Shows the wiring harness with dimensions in millimeters and tolerances.

Dimensions:

- Overall width: 43.50
- Overall height: 39.75 ± 0.11
- Width of the main body: 2.650
- Width of the handle: 12.60
- Width of the base: 6.30
- Width of the main body (bottom): 14.85
- Width of the base (bottom): 22.50
- Width of the handle (bottom): 3.70
- Width of the base (bottom): 3.50
- Width of the main body (right): 8.40 ± 0.10
- Width of the base (right): 20.70 ± 0.11
- Width of the handle (right): 10.10
- Width of the base (right): 10.10



INDICE DU PORTE-CLIPS ASSEMBLE
REVISION LEVEL OF FEMALE CONNECTOR

ZONE DE MARQUAGE
MARKING AREA

**MARQUAGES EN DESSOUS DU LEVIER
(LEVIER ENLEVE POUR CETTE VUE)
(MARKING UNDER LEVER COMPONENT
(LEVER REMOVED FOR THIS VIEW))**


LOGO DELPHI
DELPHI'S LOGO

INDICATION SORTIE FAISCEAU (DROIT)
WIRING OUT INDICATION (RIGHT)

38.20 ± 0.25
GRILLE PRE-VERROUILLEE
(POSITION DE LIVRAISON)
GRID PRE-LOCKED (DELIVERY POSITION)


34.40 ± 0.30
L
0.20 C

A



CODAGE : EN ACCORD AVEC LA SPECIFICATION NF R 13
 CODING : IN ACCORDANCE WITH NF R 13-462 SPECIFICATION
 CODAGE GRIS
 GREY CODING

INDICATION SORTIE FAISCEAU (GANG)
WIRING OUT INDICATION GANG



SORTIE FAISCEAU A GAUCHE
LEFT WIRING OUT

[illegible]

LE LEVIER CACHE LA MAUVAISE
INDICATION DE SORTIE DE FAISCEAU
LEVER HIDE BAD WIRING OUT INDICATION

SPECIFICATION DE CONDITIONNEMENT
PACKAGING SPECIFICATION

FE PA 06 013

CAHIER DES CHARGES
SPECIFICATION

NF R 13-462
FE PS 07 023

MISE EN OEUVRE
APPLICATION SPECIFICATION

DOSSIER DE PRECONISATION : PU 087
USER'S MANUAL: PU 087

DESIGN OF THE PRODUCT					
SURFACE FINISH	$\varnothing$ MINIMUM $\varnothing$	$\varnothing$ MAXIMUM $\varnothing$			
	1.30	1.50			
	1.40	1.70			
0	2.00	2.20			
0	2.10	2.40			
	2.30	2.80			
Mechanical Properties		CT 0635	CT 15		
A 90° ET 180° IND 180°		10N MAXI	12N MAXI		
		24 MINI	30 MINI		
		80N MINI	100N MINI		
PC/PL		65N MAXI			
Epoxy PC/PL		65N MAXI			
		200N MINI			
		-40°C / +125°C			
		15 g			
		±0.5 Bar IPX9K (L)			
Added in Table A (B Was A) Detailed Version Connector and Housing (D Was C) Versions, which are only produced in a version to be accordance with other customer drawings closing for automatic control					
CHANGE DESCRIPTION MODIFICATION					
COPYRIGHT : DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI COMPANY CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION OR COMMUNICATION OF THIS DOCUMENT TO ANY PARTY WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.					
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE EPREMONT, FRANCE					
DIMENSION IN MILLIMETERS DIMENSIONS EN MILLEMETRES					
DRAWING NUMBER PCC0420007					
REV. L					
SERIAL RELEASED					
See Table					

NOMENCLATURE						
PARTS LIST						
TYPE D'ETANCHEITE						
SEALING SPECIFICATION						
SORTIE FAISAU						
WIRING OUT						
REFERENCE DELPHI						
DELPHI PART NUMBER						
DELPHI INDICE						
DELPHI REVISION						
REFERENCE MVL						
MVL PART NUMBER						
MVL INDICE						
MVL REVISION						
7	GROMMET MATE SEAL	SILICONE SILICON	GRIS GREY	PP10000425		C
6	JOINT INTERFACIAL MATING SEAL	SILICONE SILICON	INCOLORE CRISTAL	PP10000428		A
5	LEVIER	PA66 GF 30	NOIR BLACK	PP10000416		A
4	GRILLE ARRIERE ETANCHE SEALED REAR GRID	PBT GF 15	GRIS CLAIR LIGHT GREY	C188300		C
3	GRILLE ARR. NON ETANCHE UNSEALED REAR GRID	PBT GF 15	GRIS FONCE DARK GREY	C288300		C
2	GRILLE AVANT FRONT GRID	PBT GF 15	NOIR BLACK	PP10000405		B (L)
2	GRILLE AVANT FRONT GRID	PBT GF 15	GRIS GREY	PP10000406		B (L)
2	GRILLE AVANT FRONT GRID	PBT GF 15	MARRON BROWN	PP10000407		B (L)
2	GRILLE AVANT FRONT GRID	PBT GF 15	VERT GREEN	PP10000408		B (L)
1	ISOLANT PORTE-CLIPS FEMALE HOUSING	PBT GF 15	NOIR BLACK	C088300		D (L)
REP.	DESIGNATION	MATIERE MATERIAL	COULEUR COLOUR	REF. MVL MVL P/N		INDICE REVISION

CODAGE NOIR BLACK CODING				CODAGE GRIS GREY CODING				CODAGE MARRON BROWN CODING				CODAGE VERT GREEN CODING			
SEALED VERSION		UNSEALED VERSION		SEALED VERSION		UNSEALED VERSION		SEALED VERSION		UNSEALED VERSION		SEALED VERSION			
GAUCHE LEFT	DROITE RIGHT	GAUCHE LEFT	DROITE RIGHT	GAUCHE LEFT	DROITE RIGHT	GAUCHE LEFT	DROITE RIGHT	GAUCHE LEFT	DROITE RIGHT	GAUCHE LEFT	DROITE RIGHT	GAUCHE LEFT	DROITE RIGHT		
13956021	13956255	33500411	35004000	33500499	33500500	33500417	35004008	33500419	33500420	33500414	35004005	33505158	33505157		
O1	O1	O1	O1	O1	O1	O1	O1	O1	O1	O1	O1	O1	O1		
PPI0001494	PPI0001495	F552100	F552100	PPI0001496	PPI0001497	F752100	F552100	F765000	F865000	F652100	F352100	F413500	F513500		
D	D	C		D	D	C		D	D	C		D	D		
I				I				I				I			
I				I				I				I			
I				I				I				I			
NA				NA				NA				NA			
I				NA				NA				NA			
NA				I				NA				NA			
NA				NA				I				NA			
NA				NA				NA				I			
I								I				I			
SEE DRAWING PCC0843002															
SEE DRAWING PCC0843002															
SEE DRAWING PCC0843002															
QTE QTY															

SEALED VERSION

UNSEALED VERSION

**SEE DRAWING
PCC0843002**

[illegible][illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[PPI0001494](#) [PPI0001495-B](#) [PPI0001496](#) [PPI0001497](#) [PPI0001494-B](#) [PPI0001496-B](#) [PPI0001497-B](#)