


SYMBOL DEFINITION			MISSING NUMBERS			DWG STATUS			ZONE	REVISION HISTORY			AUTH	DR	AP/VD	AP/VD
				DATE	STG	REV	N/P	CHG								2
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	16		22DEC99	R	01	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES AND REDRAW TO PD			198110	RB	BMC	JA
	LAST NO. USED	18		26JUN08	R	02	-	-		12124501-04, 12124507 & 12124508 OBSOLETE AND ADDED "REPLACED BY" COLUMN TO CHART			405119	EPS	FRG	RAP



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- THIS TERMINAL FOR MOLD-ON APPLICATIONS ONLY.
- TO FIT .032 X .250 BLADE.

				.0180 X 1.375		12162091	A	OBSOLETE	M1573222	X	X	X	0.8-0.5	2.4-2.03	19	102	1	.148		
				.0180 X 1.375		12124988	B	OBSOLETE	M1573222	SEE NOTE #2				0.8-0.5	2.4-2.03	19	103	1	.148	12186338
				.0180 X 1.375		12124525	C	OBSOLETE	M1573222	X	X	X	0.8-0.5	3.13-2.69	19	103	1	.148		
12124510	C	OBSOLETE		.0180 X 1.375	M1403222	12124524	C	OBSOLETE	M1573222	X	X	X	0.8-0.5	3.13-2.69	19	103	1	.148		
12124509	B	OBSOLETE		.0180 X 1.375	M1403222	12124523	B4		M1573222	X	X	X	(2) 2 - 1	3.05-2.48	215	101	1	.260		
12124508	B2	OBSOLETE		.0180 X 1.375	M1403222	12124522	B5		M1573222	X	X	X	(2) 2 - 1	3.05-2.48	215	101	1	.260	12124522	
				.0180 X 1.375		12124521	B	OBSOLETE	M1573222	X	X	X	(2) 0.8-0.5	52.4-2.03	219	101	1	.162		
12124507	B6	OBSOLETE		.0180 X 1.375	M1403222	12124520	B5		M1573222	X	X	X	(2) 0.8-0.5	52.4-2.03	219	101	1	.162	12124520	
12124504	B5	OBSOLETE		.0180 X 1.375	M1403222	12124517	B4		M1573222	X	X	X	2 - 1	3.05-2.48	15	101	1	.164	12124517	
				.0180 X 1.375		12124516	B	OBSOLETE	M1573222	X	X	X	2 - 1	3.05-2.48	15	101	1	.164		
12124503	B5	OBSOLETE		.0180 X 1.375	M1403222	12124515	B4		M1573222	X	X	X	2 - 1	3.05-2.48	15	101	1	.164	12124515	
				.0180 X 1.375		12124514	C	OBSOLETE	M1573222	X	X	X	0.8-0.5	2.4-2.03	19	103	1	.148		
12124502	C 3	OBSOLETE		.0180 X 1.375	M1403222	12124513	C2		M1573222	X	X	X	0.8-0.5	2.4-2.03	19	103	1	.148	12124513	
12124501	C 3	OBSOLETE		.0180 X 1.375	M1403222	12124512	C2		M1573222	X	X	X	0.8-0.5	2.4-2.03	19	103	1	.148	12124512	
PART NO	REV/N/P	STATUS		MAT'L SIZE	MAT'L SPEC	PART NO	REV/N/P	STATUS	MAT'L SPEC	NIB	TANG	FOOT	SIZE MM	DIA	ID	TYPE	WING CONST	E REPLACED BY		
				UNPLATED					TIN PLATED									±.015		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12124522](#) [12124523](#) [12124512-L](#) [12124515-L](#) [12124517-L](#) [12124513-L](#) [12124522-L](#) [12124523-L](#)