








SOCKET TO BE ASSEMBLED IN HOLE
SHOWN IN .0655±.0085 THICK PANEL



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE >PA66< PER SAE J1344. (.090)X(.004) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- MATING COMPONENTS OR EQUIVALENT: TERMINAL 12089661
- (.090)X(.004) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

12162711	02	AC	-	M3592001 - PA66 1M HS BLK	12004215
12162710	02	AC	-	M3592012 - PA66 1M HS GRA LT	12004347
12162709	02	AC	-	M3592008 - PA66 1M HS BLU	12004932
12162708	02	AD	OBSELETE	M3592002 - PA66 1M HS NAT	12020218
12162707	02	AC	-	M3592025 - PA66 1M HS GRA MD	12020503
12162706	A4	-	-	M3592004 - PA66 1M HS RED	12103311
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	REPLACES

(7) PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (IN)	CHART H
FROM 0	>.750 >1.250 >2.750
TO .250 1.250 2.750 4.000	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
1.000 1.000 1.002 1.008 1.000	
ANGULAR TOLERANCE ±2°	

DWS TYPE PART DRAWING	
STYLE	
VOLUME 10/15	DISTR CODE D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE IN-PROCESS DIMENSIONING AND TOLERANCE MANUAL-2001. SEPARATE NOTATIONS OF FEATURES MAY BE ADDED SEPARATELY PERMISSIBLE OF DATA REFERENCES.	
ALL DIMENSIONS ARE IN INCHES	
REFERENCE	12004348
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	UNIMPHICS

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, MI	
DR	DATE
APVD1 E. GARCIA	27FE02
APVD2 E. GARCIA	27FE02
APVD3 A. LOPEZ	27FE02
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHART	
DRAWING NAME TAXI CONN F LP SOC WEDGE W2	
DRAWING NUMBER 12162775	
SIZE A0	SCALE 5:1
FRAME NO 1	SHEET NO 1 OF 1
STG REV N/P	R 05

SYMBOL DEFINITION	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED
	14
LAST NO. USED	14

MISSING SYMBOLS		DWG STATUS				ZONE	REVISION HISTORY		AUTH	DR	APVD
		DATE	STG	REV	N/P	CHS				1	2
NO MISSING SYMBOL NUMBER		27FE02	R	001	-	-	ALL PARTS - CREATED PD & REVISED MAT'L SPEC		214864	EGR	EGR
		27FE02	R	002	-	-	ALL PARTS - .1275±.0050 WAS .125		221780	EGR	EGR
		23MY06	R	03	-	-	ALL PARTS - CORRECTED PART ECL		280325	JS	JS MEF
		27JUN06	R	04	-	-	ALL PARTS - REMOVED BLENDED EDGE UNDER LOCK FEATURE AND GROOVE UNDER FLANGE ON OUTSIDE SOCKET		282017	RH	RH MEF
		22DE06	R	05	-	-	12162708 - OBSOLETE		288187	JBD	JBD JAA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12162711](#) [12162711-B](#)