







SECTION A - A





TYPE 702
SAME AS TYPE 701
EXCEPT AS SHOWN




TYPE 703
SAME AS TYPE 701
EXCEPT AS SHOWN




TYPE 704
SAME AS TYPE 701
EXCEPT AS SHOWN



TYPE 701



SECTION B - B



SECTION C - C

REPRESENTS CLOSED POSITION
(SEE NOTE #3)

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- PARTS ARE TO BE PACKAGED IN SEALED PLASTIC BAGS. GROSS WEIGHT INCLUDING CARTON IS NOT TO EXCEED 34 POUNDS.
- "●" INDICATES CAVITY POSITION IS CLOSED. (SEE SECTION VIEW C-C)
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGES, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-C5-01.

13646875	01	AA	-	SILICONE METHYL/VINYL ORANGE	5	4	702	B	6	●	B	6	12065662	5.189
13596972	02	-	-	SILICONE METHYL/VINYL BLUE	5	5	704	8	6	8	8	8	12065662	5.160
15383475	01	AB	-	SILICONE METHYL/VINYL BLUE	5	4	702	10	7	●	10	7	12065662	5.131
15326183	B1	-	-	SILICONE METHYL/VINYL TAN	5	5	701	7	6	7	7	7	12065662	5.205
12191130	A1	-	-	SILICONE METHYL/VINYL PURPLE	5	5	701	10	8	10	10	6	12065662	5.061
12186643	A1	-	-	SILICONE METHYL/VINYL PINK	5	5	701	6	6	6	6	8	12065662	5.222
12124142	A3	-	-	SILICONE METHYL/VINYL ORANGE	5	5	701	10	7	10	10	7	12065662	5.080
12092604	B1	-	-	SILICONE METHYL/VINYL ORANGE	5	4	703	6	6	6	●	6	12065662	5.222
12084615	B	-	OBSELETE	SILICONE METHYL/VINYL BLUE	5	4	703	7	7	7	7	7	12065662	5.206
12084103	B1	-	-	SILICONE METHYL/VINYL WHITE	5	4	702	7	7	●	7	7	12065662	5.089
12077994	C1	-	-	SILICONE METHYL/VINYL RED	5	5	701	10	8	8	10	8	12065662	5.135
12066030	B1	-	-	SILICONE METHYL/VINYL YELLOW	5	5	701	10	6	6	10	6	12065662	5.127
12066029	B1	-	-	SILICONE METHYL/VINYL PURPLE	5	4	702	10	8	●	10	6	12065662	5.229
12066028	B1	-	-	SILICONE METHYL/VINYL TAN	5	4	702	6	6	●	6	6	12065662	5.229
12066027	B	-	OBSELETE	SILICONE METHYL/VINYL ORANGE	5	4	702	8	6	●	7	6	12065662	-
12066026	B	-	OBSELETE	SILICONE METHYL/VINYL BLUE	5	4	702	7	6	●	7	6	12065662	-
12065970	B1	-	-	SILICONE METHYL/VINYL RED	5	4	702	9	6	●	9	9	12065662	5.145
12065684	B1	-	-	SILICONE METHYL/VINYL GRAY	5	4	702	10	7	●	10	7	12065662	5.131
12065683	B1	-	-	SILICONE METHYL/VINYL GREEN	5	5	701	10	7	7	10	7	12065662	5.118
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	TERM CAV	CABLE HOLES	TYPE	A	B	C	D	E	TYPICAL MATING CONNECTOR (REF)	VOLUME CM ³

DRAWING NUMBER			
12077525			
SIZE	SCALE	FRAME NO	SHEET NO
A1x3	4:1	12 OF 21	7 OF 17

10	3.49-3.88
9	2.96-3.48
8	2.45-2.95
7	2.03-2.44
6	1.60-2.12
CABLE LOCATION	CABLE DIA ±0.05

THIRD ANGLE PROJECTION	DO NOT SCALE	USE MATH DATA

THIRD ANGLE PROJECTION	DO NOT SCALE	USE MATH DATA

DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH	
DATE	DATE
DR	DATE
APPROV. BY	DATE
APPROV. BY	DATE
APPROV. BY	DATE
APPROV. BY	DATE
SUBSIZES OF CONCORD ARE RECALCULATED CONTENT FOR DELPHI-A 12077525	
DRAWING TITLE TAXI SEAL CBL OW M/P	
DRAWING NUMBER 12077525	
SIZE	SCALE
A1x3	4:1
FRAME NO	SHEET NO
12 OF 21	7 OF 17
REV	REV
09	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15383475](#)