










SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	99	NO MISSING SYMBOL NUMBER
	LAST NO. USED	27	

DWG STATUS				REVISION HISTORY				AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG							
31JAO5	R	48	-	-	CLEARED REV COL AND REDRAWN TO PD1 13516904, 13521471 & 13521475 - RELEASED				264071	ESH	JAA RWR
10JNO5	R	49	-	-	ALL PARTS - REVISED PLACES ON DIMS # 2, 5, 8, 11 & 17				269150	CCV	FRG RWR
21AP06	R	50	-	-	ALL PARTS - ADDED SECTION VIEW & MOVED DIM # 15				279872	ACG	JVM RWR




NOTE: NUMBER OF DIMENSIONS WILL VARY DEPENDING ON CONNECTOR SIZE

VIEW A




TYPE 101



CORRECT MATERIAL RECYCLING CODE - SEE CHART

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (2)X(0.2) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR - SEE CHART
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
SLC - SEE CHART
- (1.73)X(0.2) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
- DO NOT USE I, O, Q & U AS CAVITY LETTERS.



VIEW SCALE DOES NOT REFLECT ACTUAL PART SIZE

13516904	01	AB	28JAO5	-	M4629002 PBT GF20 BLK	105	16	15332180/ID405536	13516906	39.1	8.078
13521475	01	AB	28JAO5	-	M4629002 PBT GF20 BLK	104	14	15332172/ID405529	13521477	35.1	7.342
13521471	01	AB	28JAO5	-	M4629002 PBT GF20 BLK	102	8	15332148/ID405513	13521473	23.1	5.162
15332176/ID405535	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	105	16	15332180/ID405536	15332181/ID405539	39.1	8.077
15332168/ID405528	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	104	14	15332172/ID405529	15332173/ID405532	35.1	7.340
15459921	01	AB	06MY03	-	M4629002 PBT GF20 BLK	103	12	15332164/ID405521	15459922	31.1	6.605
15332160/ID405520	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	103	12	15332164/ID405521	15332165/ID405525	31.1	6.604
15332144/ID405512	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	102	8	15332148/ID405513	15332149/ID405517	23.1	5.161
15459950	01	AB	06MY03	-	M4629002 PBT GF20 BLK	101	10	15332156/ID405303	15459949	27.1	5.868
15332152/ID405302	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	101	10	15332156/ID405303	15332157/ID405305	27.1	5.867
PART NO	REV	N/P	DATE	STATUS	MATERIAL SPECIFICATION AND COLOR	TYPE	CAVITIES	SLC	MATING CONNECTOR	A	VOL CM³

DIMENSIONAL RANGE (MM)		TOLERANCE UNLESS OTHERWISE SPECIFIED	
FROM	TO	±0.15	±0.2
>20	>30	±0.3	±0.4
>30	>70	±0.5	±0.6
>70	>100	±0.6	±0.8
>100	>150	±0.8	±1.0
>150	>200	±1.0	±1.2
>200	>250	±1.2	±1.5
>250	>300	±1.5	±2.0
>300	>400	±2.0	±2.5

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
APVD1 K/ENG	155E98
APVD2 R. KOCH	155E98
APVD3 R. WIS.	185E98
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 1049001	
DRAWING NAME	
TAXI CONN F 6T 150	
DRAWING NUMBER	
15326979	
SIZE	SCALE
A0	5:1
FRAME NO	SHEET NO
1 OF 1	1 OF 1
REV	N/P
R	50

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15332144](#) [15332168](#) [13521471](#) [13516904](#) [15332176](#)