



SYMBOL DEFINITION	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED
	28
	LAST NO. USED
	22



MISSING SYMBOLS		DWG STATUS					ZONE	REVISION HISTORY		AUTH	DR	APVD1	APVD2
16		DATE	STG	REV	N/P	CHG		ADDED SHT 1 OF 2; 13525425 & 13525426 - RELEASED		266261	EES	EES	MJ
		29AP05	R	06	-	-							





CORING OR MATERIAL SAVER

OPTIONAL CONSTRUCTION

TYPE 101
SAME AS TYPE 102
EXCEPT AS SHOWN




TYPE 102




NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- PARTS SHOWN ON THIS DRAWING USED IN ASSEMBLIES SHOWN ON TAXI 15406143
- REFERENCE MATING COMPONENTS OR EQUIVALENT: CONNECTOR ASSEMBLY SEE CHART.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: CONNECTOR 15404969, TERMINAL 15401440, MAX INSULATION CRIMP MUST BE LESS THAN 2 DIAMETER, SECONDARY TERMINAL LOCK 15404970, SEE DETAIL DRAWING FOR COMPATIBLE O.D. RANGE, CONNECTOR POSITION ASSURANCE LOCK 15404973
- MATERIAL RECYCLING CODE PER ISO 11469. (1)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- (1)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED" OR NO LOGO.



CORING OR MATERIAL SAVER

OPTIONAL CONSTRUCTION



DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM ³)	SEE CHART	DISTR CODE	D
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
THIRD ANGLE PROJECTION			
DO NOT SCALE			
USE MATH DATA			
UNIGRAPHICS			

DIMENSIONAL RANGE (MM)		CHART REF	
FROM	TO		
> 0	> 20	> 30	> 70
> 20	> 30	> 70	> 100
> 30	> 70	> 100	> 150
> 70	> 100	> 150	> 200
> 100	> 150	> 200	> 250
> 150	> 200	> 250	> 300
> 200	> 250	> 300	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED			
ANGULAR TOLERANCE ±2°			

13525426	01	-	-	M4695003 PBT - GRA	102	15420307	2.151	B
13525425	01	-	-	M4695002 PBT - BLK	101	15420307	2.150	A
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	TYPE	MATING CONNECTOR	VOLUME	INDEX

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
APVD1 E. SEIDEL	29AP05
APVD2 E. SEIDEL	29AP05
APVD3 MAURO JADUE	06MY05
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI-A 10949001	
MATERIAL SEE CHART	
DRAWING NAME TAXI CONN F MICRO 64	
DRAWING NUMBER 15435207	
SIZE A1	SCALE 2:1
FRAME NO 1 OF 1	SHEET NO 1 OF 2
STG R	REV 06
N/P -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13525426](#)