





VALIDATED ACCORDING: GMI 12590
GEPRUEFT NACH: GMI 12590

NEUTRAL VERSION

DCSI 9.5MM FEMALE TERM.	6 007 02 71	10763018	>6.00 - 10.00	Ø 5.80 - Ø 6.60	6 099 33 03	10721071	3, 5
				Ø 5.40 - Ø 6.60	6 099 33 04	10889241	
				Ø 3.50 - Ø 5.50	6 099 33 01	15327788	
	6 007 02 61	15327734	>4.00 - 6.00	Ø 3.40 - Ø 4.40	6 099 33 08	13546490	
				Ø 3.50 - Ø 5.50	6 099 33 01	15327788	
	6 007 02 51	10775312	>2.50 - 4.00	Ø 3.50 - Ø 5.50	6 099 33 01	15327788	
			Ø 3.40 - Ø 4.40	6 099 33 08	13546490		
DCSI 6.3MM FEMALE TERM.	6 004 00 51	10748126	4.00	Ø 3.10 - Ø 5.50	6 099 26 06	12186636	1, 2
	6 004 00 41	15340695	1.50 - 2.50	Ø 2.20 - Ø 3.20	6 099 26 04	15443869	
	6 004 00 31	12186637	0.50-0.75-1.00	Ø 1.40 - Ø 2.30	6 099 26 07	12186638	
DCSI 2.8MM FEMALE TERM.	6 004 05 41	33511768	>1.00 - 1.50	Ø 2.20 - Ø 2.70	6 099 34 05	33501746	6,7,8,9
	6 001 05 31	12198447	0.50 - 1.00	Ø 1.70 - Ø 2.10	6 099 34 03	15327786	
	6 001 05 11	15395924	0.35	Ø 1.20 - Ø 1.60	6 099 34 01	33511807	
DESCRIPTION	MVL	DELPHI	WIRE SIZE DRAHTGROSSEN- BEREICH (mm ²)	ISOLATION SIZE ISOLATIONSBEREICH (Ø)	MVL	DELPHI	CAVITY-NO. KAMMER-NR.
	PART-NO. TEILE-NR.				PART-NO. SINGLE WIRE SEAL Einzeladerdichtung		
USEABLE TERMINALS FOR THIS CONNECTOR GEEIGNETE KONTAKTE FUER DIESEN STECKER							

13-00711	A5	DPN 33511769 REPLACED BY 33511807		
ECN-NO. ECN-NUMBER	POSITION POSITION	CHANGE DESCRIPTION ÄNDERUNGSBESCHREIBUNG		
PRODUCT SPEC. PRODUKT-SPEZ.	PACKAGING SPEC. VERPACKUNGS-SPEZ.	APPLICATION SPEC. ANWENDUNGS-SPEZ.	COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED PATENT INFORMATION: THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION OR COMMUNICATION OF THIS DOCUMENT OR ITS RELATED CAD DATA DATA, AS WELL AS UTILIZATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
		9 902 07 40	THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION OR COMMUNICATION OF THIS DOCUMENT OR ITS RELATED CAD DATA DATA, AS WELL AS UTILIZATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
TOLERANCES TOLERANZ	DIN ISO 2768 T1 DIN ISO 2768 T2	MATERIAL : MATERIAL : SEE TABLE FARB : FARB : SIEHE TABELLE	SURFACE FINISH OBERFLÄCHE	
COUNTERPART No. GEGENSTÜCK-Nr.	SEE NOTES	COLOR : FARB :	DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE NÜRNBERG, GERMANY	
DO NOT MEASURE DRAWING ZEICHNUNG NICHT VERMESSEN	DATE DATUM	NAME NAME	ECO Loc. Code STANDORT CODE GN	CAD SYSTEM pro1 eng.
CREATED BY ERSTELLT	1996-05-05	WEL	DIMENSION IN MILLIMETERS BEMASSUNG IN MILLIMETER	
MODIFIED BY GEÄNDERT	2013/06/19	M WELTHER	ISO PROJECTION ISO PROJEKTION	
CHECKED BY GEPRÜFT	2013/06/19	M SCHINDLER	DRAWING NUMBER ZEICHN. -NUMMER	
APPROVED BY GEBILDIGT	2013/06/19	Olaf HOERNLEIN	REV. INDEX	
FILE NAME DOK.-NAME	60431011C	28WAY SEALED FEMALE CONNECTOR	APPROVAL LEVEL FREIGABESTUFE	
		28WAY SEALED FEMALE CONNECTOR	SHEET BLATT	
		28WAY SEALED FEMALE CONNECTOR	of 1 100	
		28WAY SEALED FEMALE CONNECTOR	SCALE MASSSTAB	
		28WAY SEALED FEMALE CONNECTOR	2:1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15443869](#) [12186636](#)