

Specifications		Mating Half
<div><div></div><div></div></div>	General	MechanicalPhysicalTerminal 1 TypeEnvironmentalOther Features
<div>General</div>		
Application	Component to Wire Wire to Wire Engine Compartment Connectors	
Ways	2	
Product Type	Housing	
Coding	No	
Features	Female terminal protected by box Mechanical polarization Circumferential interface seal Additional terminal locking device pre-assembled on front part of the housing Plastic locking feature Sealing protection IP 67 Waterproof application with Single Wire Seal (S.W.S.) Acceptable wire size range from 6 to 10 mm² Terminal position assurance (T.P.A.) and connector position assurance (C.P.A.)	
Hybrid	No	
Main Terminal family	DCS-1	
Main Terminal size	9.5 mm	
Sealed	Yes	
Terminal Size	9.5	
Mechanical		
Connector mating force	< 75 N	
Physical		
Color	Black	
Material	PBT	
Temperature (Range)	-40 °C to +120 °C	
Terminal 1 Type		
Terminal type 1	DCS-1 Box Female 9.5 mm Terminal	
Ways for Terminal Type 1	2	
Contact insertion force for Terminal Type 1	< 30 N	
Retention force (Contact) for Terminal Type 1	> 80N	
Environmental		
IMDS	Yes	
Other Features		
Market	Passenger Vehicles	
Type	Female	
Part Situation	Active	
Disclaimer	Displayed data is for information purposes only. For more information, please contact your local sales office. The supply of some products might be limited to some customers.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[F064200](#)