







TYPE 111
SAME AS TYPE 10.
EXCEPT AS SHOWN




TYPE 110
SAME AS TYPE 10.
EXCEPT AS SHOWN




TYPE 109
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 108
SAME AS TYPE 10
EXCEPT AS SHOWN




TYPE 107
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 106
SAME AS TYPE 10
EXCEPT AS SHOWN




TYPE 105
SAME AS TYPE 10
EXCEPT AS SHOWN



TYPE 104
SAME AS TYPE 10
EXCEPT AS SHOWN





TYPE 103
SAME AS TYPE 10
EXCEPT AS SHOWN




TYPE 102
SAME AS TYPE 10
EXCEPT AS SHOWN

MATERIAL RECYCLING CODE - SEE CHART—



TYPE 101



- NOTES
1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 2. SEALING CODE 3 - DESIGN WILL PASS SALT FOG AND IMMERSION
TEST AFTER CONDITIONING AS SPECIFIED IN
ESA-644 (WEATHER-PACK), ESA-710 (METRI-PACK),
ESA-650 (UNDERHOOD MICRO-PACK), C-4006
(WORLD CONNECTOR), ETC WHEN MATED TO
MATING PART OR EQUIVALENT
 3. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:

TERMINAL - 15482808 OR 15326267 (18 GA), 15423490 OR 15326266 (20/22 GA)
CABLE SEAL - 15305151 (18 GA), 15366022 (20/22 GA)
○ CAVITY PLUG - 15305171
TERMINAL POSITION ASSURANCE LOCK - 15305028
 4. WHEN PARTS ARE SHIPPED THEY MUST BE PACKED IN PLASTIC BAGS
OR SHIPPING CONTAINERS MUST BE LINED WITH PLASTIC LINERS.
BAGS OR LINERS MUST BE SEALED TO AVOID FOREIGN MATTER.
 5. FOR MATING CONFIGURATION REQUIREMENTS SEE DRAWINGS
15335900, 15336019



15439568	01	AD	108	15366040	15439567	12040756			PBT
15436719	01	AD	110	15436720	15326558	12040756	B	AND	D
15436717	01	AD	111	15436718	15326558	12040756	A	AND	C
15423593	01	AD	109	15423592	15326558	12040756	A	AND	D
15413116	02	AE	108	15366040	15336003	12040756			PBT
15410728	01	AH	107	15366040	15326558	12040756			PBT
15366027	02	AH	106	15366028	15326558	12040756	B	AND	D
15366025	02	AH	106	15366026	15326558	12040756	A	AND	C
15354716	A10	-	104	15354717	15326558	12040756			PAG-GB20 GF10
15336842	02	AH	103	15336845	15326558	12040756			PAG-GB20 GF10
15336848	A10	-	102	15336849	12040756	12040756	C		PAG-GB20 GF10
15336846	A10	-	101	15336847	15326558	12040756	B	AND	D
ASB PART NO	REV	N/P	STATUS	TYPE	CONNECTOR	PLR	SEAL	BLOCKED CAVITIES	MATERIAL RECYCL CODE

SYMBOL DEFINITION	
WITHOUT AN INSPECTION REPORT SYMBOL T REQUIRE INSPECTION. IT MAY BE ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL INSPE REQUIR
	LAST USED

		MISSI
NO OF CTIONS RED	11	
NO.	12	

NG SYMBOLS	DATE
7	02MY
	21JN
	09DE

DIS STATUS	DATE	TIME	BY	ZONE	REVISION HISTORY	AUTH	DR	APPV	CHK
02	R	12	-	-	CLEARED REVISION COLUMN: 15436717 AND 15436719 - RELEASED	2254587	JAA	JAA	EAH
02	R	13	-	-	ALL PARTS - REVISION NOTE 5 : 15439568 - RELEASED	2254847	JAA	JAA	EAH
02	R	14	-	-	15439568 - CONNECTOR PART NUMBER WAS 15336040	2142423	LDL	LDL	EAH
03	R	15	-	-	ALL PARTS - REVISION NOTE 3	2502225	EEB	EEB	EAH
03	R	16	-	-	15438719 - WAS TYPE 105; 15436717 - WAS TYPE 106; ALL PARTS - REVISION NOTE 106: ALL PARTS - REVISION NOTE TO CHART	2703937	CPJ	CPJ	EAH
06	R	17	-	-	ALL PARTS - REVISION NOTE 3 CAVITY MATERIAL WAS 15392615	2810666	RMB	JAA	EAH

[illegible]

DELPHI					
WAFER ELECTRIC SYSTEMS					
WARREN, OH					
DATE _____					
09F9E9B					
09F9E9B					
ON _____					
OF CONCERN AND RECYCLED					
PER DELPHI (1994900)					
CONN F OT 150 SLID					
A					
336850					
FRANK TO		SHIRT NO		STG	REV
OF 2		1 OF		R	17

1233020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15336864](#)