




RUBBER PART GENERAL TOLERANCE			
PART DIM.	1	2	3
0 TO 3	±0.2	±0.3	±0.4
3 TO 6	±0.2	±0.4	±0.5
6 TO 10	±0.3	±0.5	±0.6
10 TO 18	±0.3	±0.6	±0.8
18 TO 30	±0.4	±0.8	±1.0
30 TO 50	±0.5	±1.0	±1.5
50 TO 80	±0.6	±1.2	±2.0
80 TO 120	±0.7	±1.4	±2.5
120 TO 180	±0.8	±1.6	±3.0
180 TO 250	±1.0	±2.0	±4.0
250 TO 315	±1.2	±2.5	±5.0
315 TO 400	±1.5	±3.0	±6.0
400 TO 500	±1.8	±3.5	±7.0
500 OVER	±0.4%	±0.8%	±1.5%

NOTES:

- 1. MATERIAL: EPDM
- 2. COLOR: BLACK

	2020/11/04	NEW	C20-A781	J.B.
LET	DATE	REVISION RECORD	NO.	CHKD

©2020 YAZAKI NORTH AMERICA, INC. ALL INFORMATION ON THIS DRAWING IS THE PROPRIETARY AND CONFIDENTIAL PROPERTY OF YNA AND SHALL NOT BE DISCLOSED, DUPLICATED OR DISTRIBUTED WITHOUT THE EXPRESS WRITTEN CONSENT OF YNA. ALL RIGHTS RESERVED.							
GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.5°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±1.0°	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±1.5°	0.15
SPECIFIED						MASS	
SEE RUBBER PART TOLERANCE CHART						81.2 g	

CUSTOMER						
CUSTOMER PART NO.						
CUSTOMER DWG NO.						
OFFICE YNA-L				TRIAL PART NO.		
VENDOR				-----		
VENDOR NO.				-----		
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	
R	NEW	2020/11/04	mm	1 / 1	3	
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		
			NOMOTO			
			2018/10/19			

MATL. SPEC.		SEE NOTES	TREAT. & FIN.	
NAME FRONT DOOR GROMMET				
PART NO. 7035-0694-30				
DWG NO. 7035-0694-30:R				SET DWG NO.
YAZAKI CORPORATION				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yazaki:](#)

[7035069430](#)