







YAZAKI SUBASSY NO.	NO.	YAZAKI PART NUMBER	PART NAME	MATERIAL	COLOR	QTY
7286-1657-30	3	7157-1298-50	PACKING (M)	SILICONE RUBBER	RED	1
	2	7158-6832-70	FRONT HOLDER (H)	PBT-GF15	YELLOW	1
	1	7185-1657-30	TOP HOUSING (H)	PBT-GF15	BLACK	1

NOTES:

1. MATERIAL: SEE TABLE;
2. COLOR: SEE TABLE;
3. APPLICABLE TERMINALS: TERMINAL No. 211CL251160 AND 211CL252160;
4. APPLICABLE SEALS: SEE TABLE;
5. THIS DIMENSION SHOWS THE PRESET POSITION OF FRONT HOLDER ON THE SUBASSEMBLY;
6. MATING PART ACCORDING DRAWING: 19201E710NT1;
7. FOR GENERAL GEOMETRICAL TOLERANCE SEE TABLE (ECCENT=ECCENTRICITY);
8. HANDLING MANUAL: TBD;
9. PRODUCT STANDARD: TBD;
10. THE MATERIALS USED IN THIS PRODUCT SHOULD BE IN CONFORMITY WITH REQUIREMENTS OF EU ELY 2000/53/EC DIRECTIVE AND ASSOCIATED DOCUMENTS AND "CONTROL STANDARD FOR CHEMICAL SUBSTANCE (Y65-L21-010)".
11. PRINTED COPIES ARE UNCONTROLLED. THEY ARE POTENTIALLY OUT-OF-DATE AND INVALID. DATABASE IS MASTER.



SECTION A-A



ISOMETRIC VIEW
(SCALE 1:1)

Δ	08/10/30	CHANGED FORM AND MAT	Y08-0196	V.M.
Δ	08/01/23	CHANGED FORM	C08-0538	V.M.
Δ	01/01/04	NEW	C07-0504	V.M.

LET	DATE	REVISION RECORD	NO.	CHKD
			1	

GENERAL TOLERANCE

A	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15
SPECIFIED							
						MASS	

CUSTOMER PART NO.	CUSTOMER DWG NO.	MAT. SPEC.	SEE NOTES	TREAT. & FIN.	ISSUE MARK
OFFICE YEL-K	TRIAL PART NO.	NAME	1.5 SICMA3 SYSTEM CONNECTOR		
VENDOR NO.		10P (M) SUBASSY			

APPROVED	CHECKED	DESIGN	DRAWN	PART NO.	7286-1657-30	CH. CODE		SET DWG NO.	
STERN LEN R. RESMAN V. VAKHOTIC R. JORIC T. REBIC				DWG NO.	7286-1657-30:R				

3

4

5

A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yazaki:](#)

[7286165730](#)