



- A. Threaded tip.
- B. 10-32 female threaded probe socket will accept any 10-32 threaded tip.
- C. Audio output is 2 KHz signal.
- D. Operated with two AAA batteries (included). Body is black butyrate plastic.
- E. Test lead is 42" (1.1m) long, high flex strand copper 20 gauge, with black PVC insulated jacket.

- F. Molded Banana Plug. Can be used to plug directly into banana jack. Will also accept any attachment designed for use with standard banana plug.
- G. Alligator Clip – included probe attachment for use with Molded Banana Plug (F).

Electrical specifications:

Maximum probe voltage - 3 VDC
 Probe current = 15 ma
 Range - 0-50 ohms

Battery Replacement Instructions:

Unscrew the top of the Circuitracer® in counter clockwise direction. Replace the two AAA batteries in the handle with the positive terminals facing up. Replace the top in the clockwise direction.

Specifications and procedures subject to change without notice.



Made in the
 United States of America

CIRCUITRACER® CONTINUITY TESTER, AUDIBLE, 0 - 50 OHMS

MENDA

3651 WALNUT AVE., CHINO, CA 91710
 PHONE: (909) 627-2453 FAX: (909) 755-8848
 WEBSITE: MendaPump.com

**DRAWING
 NUMBER**
 35135

DATE:
 September
 2011

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Menda:](#)

[35135](#)