



- A. Threaded tip.
- B. 10-32 female threaded probe socket will accept any 10-32 threaded tip.
- C. Audio output is 2 KHz signal.
- D. Operated with two AAA batteries (included). Body is black butyrate plastic.
- E. Test lead is 42" (1.1m) long, high flex strand copper 20 gauge, with black PVC insulated jacket.

- F. Molded Banana Plug. Can be used to plug directly into banana jack. Will also accept any attachment designed for use with standard banana plug.
- G. Alligator Clip – included probe attachment for use with Molded Banana Plug (F).

**Electrical specifications:**  
 Maximum probe voltage - 3 VDC  
 Probe current = 15 ma  
 Range - 0-50 ohms

**Battery Replacement Instructions:**  
 Unscrew the top of the Circuitracer® in counter clockwise direction.  
 Replace the two AAA batteries in the handle with the positive terminals facing up. Replace the top in the clockwise direction.

Specifications and procedures subject to change without notice.



Made in the  
United States of America

**CIRCUITRACER® CONTINUITY TESTER, AUDIBLE, 0 - 50 OHMS**

**MENDA**

3651 WALNUT AVE., CHINO, CA 91710  
 PHONE: (909) 627-2453 FAX: (909) 755-8848  
 WEBSITE: [MendaPump.com](http://MendaPump.com)

**DRAWING  
NUMBER**  
35135

**DATE:**  
September  
2011

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Desco:](#)

[35135](#)