



Tolerances:
All dimensions +/- .125"


STORAGE CONTAINERS

• These items made to order

Item No.	REF#	Box Size I.D. - L x W x D	Handles	Lid	Wire	Foam
37508	411-BX	16-7/8 x 10 x 3-1/2 IN (429 x 254 x 89 MM)	N/A	37550	N/A	37451
37501	401-BX	16-7/8 x 10 x 5-3/8 IN (429 x 254 x 137 MM)	N/A	37550	N/A	37451
37509	422-BX	17 x 9-7/8 x 2-1/2 IN (432 x 254 x 137 MM)	N/A	37550	N/A	37451
37500	400-BX	17 x 9-7/8 x 7-1/4 IN (432 x 251 x 184 MM)	37450	37550	N/A	37451
37512	438-BX	17 x 13 x 8-3/4 IN (432 x 330 x 222 MM)	37450	37551	37456	37452
37520 •	456-BX	18-3/8 x 12-3/8 x 6-3/4 IN (467 x 314 x 171 MM)	37450	37553	37458	37454
37505	405-BX	18-1/2 x 12-3/8 x 18-3/4 IN (470 x 314 x 476 MM)	37450	37553	37458	37454
37506	406-BX	18-5/8 x 15 x 5-7/8 IN (473 x 381 x 149 MM)	37450	37554	37459	37455
37527	468-BX	18-5/8 x 15 x 8 IN (473 x 381 x 203 MM)	37450	37554	37459	37455
37524	460-BX	18-5/8 x 15 x 10 IN (473 x 381 x 254 MM)	37450	37554	37459	37455
37525	462-BX	18-5/8 x 15 x 12 IN (473 x 381 x 305 MM)	37450	37554	37459	37455
37526	464-BX	18-5/8 x 15 x 14 IN (473 x 381 x 356 MM)	37450	37554	37459	37455
37516	446-BX	22-7/8 x 12-7/8 x 6 IN (581 x 327 x 152 MM)	37450	37552	37457	37453
37517	448-BX	22-7/8 x 12-7/8 x 8 IN (581 x 327 x 203 MM)	37450	37552	37457	37453
37514	440-BX	22-7/8 x 12-7/8 x 10 IN (581 x 327 x 254 MM)	37450	37552	37457	37453
37504	404-BX	22-7/8 x 12-7/8 x 12-5/8 IN (581 x 327 x 321 MM)	37450	37552	37457	37453
37515	445-BX	22-7/8 x 12-7/8 x 15-1/4 IN (581 x 327 x 387 MM)	37450	37552	37457	37453
37530		21-7/8 x 18-7/8 x 4-1/4 IN (556 x 479 x 108 MM)	N/A	37557	N/A	N/A
37532		22 x 18-7/8 x 8 IN (559 x 480 x 203 MM)	N/A	37557	NA	N/A



Conductive Plastic
Handles



Permanently static dissipative
crosslink bottom foam to
cushion circuit boards



Steel wire perimeter
reinforcing frame for extra
strength and durability

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Protektive Pak:

[37504](#) [37557](#) [37532](#) [37530](#)