

6800 Series Dissipative Rubber Mats and Runners



The 6800 Series Static Dissipative Rubber Mats and Runners meets ANSI/ ESD S20.20 worksurface required limit (and recommendation of ANSI/ESD S4.1), tested per ANSI/ESD S4.1 and ESD TR53. The 6800 Series mats provide the durability you expect from a dual-layer rubber mat at a very competitive cost. Featuring a smooth finish, the 6800 Series Static Dissipative Rubber Mats and Runners are available in blue/black and gray/black colors, and feature standard sizes in 2 feet, 3 feet and 4 feet widths and 50 feet lengths. In addition, they are also available in 2 feet x 4 feet cut mats in blue/black and gray/black, including snaps.



Properties	Typical Value	Test Method
Material	Nitrile	
Thickness*	0.072" (1.8 mm)	
Color* (Top / Bottom)	Blue / Black Gray / Black	
Hardness (top)	65 Shore A	
*Resistances Surface to Ground (Rtg) Surface to Surface (Rtt)	<10 ⁹ ohms <10 ⁹ ohms	ANSI/ESD S4.1 ANSI/ESD S4.1
Tolerance	Width +/- 0.250" Length +/- 0.250"	

*Color, texture and thickness may vary between lots and mills.

Table Mat Kit Item Numbers

Size	Blue	Gray
2' X 4' (0.6 m X 1.2 m)	6811	6810

Table Mat Kit Includes:

- 1 Table Mat, size as specified
- 2 [3034](#) Snap Fasteners (installed)

Runner Item Numbers

Size	Blue	Gray
2' x 50' (0.6 m x 15.2 m)	6841	6840
3' x 50' (0.9 m x 15.2 m)	6861	6860
4' x 50' (1.2 m x 15.2 m)	6871	6870

Mat rolls need to be unrolled before being cut. When rolled, some shrinkage may occur. Please allow time for mat to relax at room temperature 24-48 hours prior to cutting.

Made in China

Specifications and procedures subject to change without notice.

6800 SERIES DISSIPATIVE RUBBER MATS AND RUNNERS

SCS

926 JR Industrial Drive, Sanford, NC 27332
WEB SITE: StaticControl.com
PHONE (919) 718-0000

**DRAWING
NUMBER**
6800

DATE
August
2015

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SCS:

6840 6870