



#### Dimensional Tolerances:

Core Length:  $\pm 1/16$ "

Paper Width:  $\pm 1/8$ "

Core ID:  $\pm 1/8$ "

Paper Length:  $\pm 5\%$

EasyBraid expressly warrants that for a period of one (1) year from the date of purchase, EasyBraid products will be free of defects in material (parts) and workmanship (labor). Within the warranty period, a unit/product will be tested, repaired or replaced at EasyBraid's option, free of charge.

Specifications and procedures subject to change without notice.

## Features

- Under Stencil Rolls for MPM Printers
- Prevents smearing, bridging, solder balls, and other problems associated with the stencil printing of solder paste
- Manufactured from a blend of polyester and cellulosic fibers
- More paper per roll resulting in less down time, less changeover time, and less inventory required
- Exceptionally low lint levels
- Solvent resistant material results in increased absorption per square inch



## MPM Paper Specifications

Test	Orientation	Units	Value	Method
Composition			54% Wood Pulp 46% Polyester White	
Basis Weight		oz/yd <sub>2</sub> g/m <sub>2</sub>	1.5 50.8	ASTM D3776
Thickness		mils mm	12 .30	ASTM D1777
Grab Tensile Strength	Machine Direction	lb N	28 125	ASTM D5034
	Cross Direction	lb N	16 71	

## MPM Stencil Roll Part Numbers

Part Number	Core Type	Core Length	Paper Width	Core ID	Paper Length
EB41M1809	Paper	18"	8.75"	.765"	55'
EB41M1812	Paper	18"	12"	.765"	55'
EB41M1814	Paper	18"	14"	.765"	55'
EB41M1818-1	Paper	18"	17.50"	1.00"	47'
EB41M1855	Paper	18"	17.50"	.765"	55'
EB41M2025	Paper	20.25"	20.25"	.765"	55'
EB41M2222	Paper	22"	21.62"	.765"	55'
EB41M2424	Paper	24"	23.62"	.765"	55'

## MPM STENCIL ROLLS

115420 K-TEL DRIVE, MINNETONKA, MN 55343  
PHONE: (909) 627-2453  
WEBSITE: [EASYBRAIDCO.COM](http://EASYBRAIDCO.COM)

**DRAWING  
NUMBER**  
MPM

**DATE:**  
January  
2020

# EasyBraid

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Menda:

[EB41M1812](#) [EB41M1855](#) [EB41M2424](#) [EB41M2222](#) [EB41M1809](#) [EB41M1814](#) [EB41M1818-1](#)