

STATICO

Product Specifications for S101-09 & S101-12 Static Dissipative PP Strap



Specifications

Material	Polypropylene Co-Polymer
Color	Black
Resistance	10^5-10^8 ohm/sq
Standard Roll Sizes	9mm (0.354") Wide x1200 Meter (3937') Long 12mm (0.472") Wide x 1500 Meter (4895') Long
Thickness	0.025" (0.6mm, +/-0.1mm)
Melting Point	338° F, +/-41° F (170° C, +/-5° C)
Tensile Strength	72.0 MPA (Before Bake) & 68 MPA (After Bake)
Core Diameter	7" (200mm)
Features	*Minimum Shrinkage of Straps after baking process *Compatible with most strapping machines *Excellent electrical properties
Application	Suitable for Strapping of IC trays/tubes during burn-in test and transportation

Note: Tolerances +/- 10%

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Desco:](#)

[S101-12](#) [S101-09](#)