


OIL TIGHT Large Incandescent Indicators

FOR MOUNTING IN 1" CLEARANCE HOLE


For materials and finishes of products in this group, see preceding page.



C7
DOUBLE CONTACT
BAYONET BASE

☐ Movable and Fixed Terminals:
see preceding page.

LAMP NO.	VOLTS	WATTS	HOURS
10C7/1DC	120	10	6000
10C7/5DC	120	10	8000
10C7/DC	120	10	6000



103-3427-0531-403
Torpedo lens

Recognized under the component
program of Underwriters'
Laboratories Inc.



103 SERIES

BASE PART NUMBERS

movable screw terminals	fixed screw terminals	fixed soldering terminals
<p>1/16 PANEL (REF.) 0.025 ± .005 X 1.3/8 ± .020 O.D. INTERNAL TOOTH LOCKWASHER 1/8 X 1-1/8 ACROSS FLATS HEX. NUT. "O" RINGS 1-27 NS THD. MOUNTING BUSHING 6-32 THD. PROJECTION BACK OF PANEL 5/64 X 1-3/16 O.D. FLANGE 2-1/4 MAX.</p>	<p>6-32 NC THD.</p>	<p>3/32 DIA. (2 HOLES)</p>
103-3527-05-103	103-3227-05-103	103-3427-05-103

CAP PART NUMBERS

COMPLETE ASSEMBLY PART NUMBERS

<p>1-27 NS THD. (INTERNAL) 1-13/64 63/64 MAX.</p> <p>TORPEDO 103-0531-403 unfrosted 103-0511-403 back frosted</p>	103-3527-0531-403	103-3227-0531-403	103-3427-0531-403
<p>1-27 NS THD. (INTERNAL) 1-13/64 1 MAX.</p> <p>TORPEDO FACETED 103-1331-403 unfrosted</p>	103-3527-1331-403	103-3227-1331-403	103-3427-1331-403
<p>1-27 NS THD. (INTERNAL) 1-13/64 7/8 MAX.</p> <p>DOME 103-1231-403 unfrosted 103-1211-403 back frosted</p>	103-3527-1231-403 103-3527-1211-403	103-3227-1231-403 103-3227-1211-403	103-3427-1231-403 103-3427-1211-403

☐ For movable soldering terminals, change the group of digits of the part number that reads -3527- to -3627-.
Example: 103-3627-0531-403.

Part numbers shown in gray are normally
in inventory at your Dialight Distributor.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[103-3227-05-103](#) [103352705103](#)