


521 SERIES INCANDESCENT LAMPS

T-3 1/4 MINIATURE BAYONET BASE

PART NO.	LAMP NO.	VOLTS	AMPS	MSCD	LIFE HOURS
-	49	2.0	.06	0.04	1,000
-	45	3.2	.35	0.50	3,000
-	47	6.3*	.15	0.50	3,000
-	1847	6.3*	.15	0.38	3,000
-	44	6.3*	.25	0.90	3,000
-	1866	6.3*	.25	0.65	20,000
521-0755	755	6.3*	.15	0.33	20,000
-	1891	14.0*	.24	2.0	500
521-1815	1815	14.0*	.20	1.4	3,000
521-0756	756	14.0*	.08	0.31	15,000
-	1819	28.0*	.04	0.34	2,500
-	1829	28.0*	.07	1.0	1,000
-	1820	28.0*	.10	1.6	1,000
521-0313	313	28.0*	.17	3.5	500
521-0757	757	28.0*	.08	0.62	7,500
-	1828	37.5	.05	0.65	3,000
521-1835	1835	55.0	.05	1.1	5,000
521-9109	120MB	120.0*	.025	0.36	10,000



T-3 1/4 MINIATURE BAYONET BASE INCANDESCENT LAMP

* Also available in T-3 1/4 multichip and T 3 1/4 cluster Based LED versions. See pages 39 and 40 for information.

Note: 120 volt version only available in T-3 1/4 cluster version. See page 40 for information.

S-6 DOUBLE CONTACT BAYONET BASE

PART NO.	LAMP NO.	VOLTS	AMPS	LIFE HOURS
-	6S6DC-24V	24	0.025	3,000
-	6S6DC-30V	30	0.2	3,500
-	6S6DC-48V	48	0.125	3,500
521-9080	6S6DC-75V	75	0.08	3,000
521-9081	6S6DC-125V	125	0.05	4,000
-	6S6DC-135V	135	0.05	3,000
-	6S6DC-145V	145	0.04	3,800
-	10S6DC-230V	230	0.04	3,000
521-9096	10S6DC-250V	250	0.04	3,000



S-6 DOUBLE CONTACT BAYONET BASE INCANDESCENT LAMP

S-6 CANDELABRA SCREW BASE

PART NO.	LAMP NO.	VOLTS	AMPS	LIFE HOURS
521-9062	6S6-6V	6	1.0	3,000
521-9063	6S6-12V	12	0.5	3,000
521-9064	6S6-24V	24	0.25	3,000
-	6S6-30V	30	0.2	3,500
-	6S6-48V	48	0.125	3,500
-	6S6-75V	75	0.08	3,000
521-9068	6S6-125V	125	0.05	4,000
521-9072	6S6-135V	135	0.05	3,000
-	6S6-145V	145	0.04	3,800
-	10S6-230V	230	0.04	3,000



S-6 CANDELABRA SCREW BASE INCANDESCENT LAMP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[521-0382](#) [521-0370](#) [521-9109](#) [521-0330](#) [521-0327](#) [521-0328](#) [521-0387](#) [521-0345](#)