





OPERATING CHARACTERISTICS AT 25°C AMBIENT											
COLOR	LUMINOUS INTENSITY @ If = 10 mA (mcd)			FORWARD VOLTAGE TEST CONDITION	FORWARD VOLTAGE (V)		REVERSE VOLTAGE (If=10μA)	DOMINANT WAVELENGTH (nm)			PEAK WAVELENGTH (nm)
	MIN	TYP	MAX		TYP	MAX	MIN	MIN	TYP	MAX	TYP
HI. EFF. RED	5.6	9.8	14.0	If = 10 mA	2.0	2.5	12 V	622	628	634	635
AlGaAs RED	21.6	38.0	56.0	If = 10 mA	1.8	2.5	12 V	—	645	—	660
HI. INT. GREEN	13.8	24.0	35.8	If = 10 mA	2.0	2.5	12 V	564	570	576	572
GREEN	7.1	10.6	14.0	If = 10 mA	2.0	2.5	12 V	564	570	576	572
YELLOW	7.1	12.6	18.0	If = 10 mA	2.0	2.5	12 V	580	587	595	586
ORANGE	4.5	8.0	11.6	If = 10 mA	2.0	2.5	12 V	600	606	609	610
BLUE	7.6	12.0	20.0	If = 10 mA	3.5	4.2	5 V	462	465	468	428
AlInGaP YELLOW	40.0	62.0	—	If = 20 mA	2.0	2.4	12 V	580	587	595	591
WHITE	80	130	210	If = 10 mA	3.1	3.7	5 V		X .33 Y .33		—
InGaN GREEN	85	160	—	If = 20 mA	3.4	4.05	5 V	515	525	535	523

ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT						
COLOR	POWER DISSIPATION (mW)	CONTINUOUS FORWARD CURRENT (mA)	PEAK FORWARD CURRENT (I ≤ 10μs, D = .005) (mA)	DERATE LINEARLY (mA/°C)	OPERATING TEMPERATURE (°C)	STORAGE TEMPERATURE (°C)
HI. EFF. RED	95	30	500	0.75 FROM 60°C	-40 TO +100	-40 TO +100
AlGaAs RED	90	30	500	0.75 FROM 60°C		
HI. INT. GREEN	95	30	500	0.75 FROM 60°C		
GREEN	95	30	500	0.75 FROM 60°C		
YELLOW	95	30	500	0.75 FROM 60°C		
ORANGE	95	30	500	0.75 FROM 60°C		
BLUE	90	20	200	0.44 FROM 55°C		
AlInGaP YELLOW	80	30	200	1.0 FROM 85°C		
WHITE	80	20	200	0.75 FROM 60°C	-55 TO +100	-55 TO +100
InGaN GREEN	115	30	100 (I ≤ 1.0ms, D = 0.1)	0.42 FROM 40°C		




RECOMMENDED RoHS COMPLIANT REFLOW PROFILE


1. MILLIMETER DIMENSIONS SHOWN FOR REFERENCE ONLY.
2. PAD NUMBERS ARE FOR REFERENCE ONLY , DESIGNATION NON-EXISTENT ON PART.
3. STORAGE CONDITIONS FOR TAPED PRODUCT: RE-TAPING MAY BE NECESSARY FOR PRODUCTS STORED MORE THAN TWELVE MONTHS.
4. ORDER QUANTITY IS LED ASSEMBLIES, NOT REELS.
5. ...-102F SUFFIX MEANS PARTS ARE PACKED ON A 20 pc SAMPLE STRIP
...-107F SUFFIX MEANS PARTS ARE PACKED ON A 7 INCH REEL , 400 pcs/REEL
...-113F SUFFIX MEANS PARTS ARE PACKED ON A 13 INCH REEL , 1600 pcs/REEL
6. LENS MOVEMENT IN RELATIONSHIP TO THE HOUSING IS:
 .009" T.I.R. VERTICALLY
 .007" T.I.R. HORIZONTALLY
7. FRONT AND REAR TERMINALS OF THE ASSEMBLY TO BE WITHIN .005 COPLANARITY.
8. DIALIGHT PART NUMBERS = 591-2x01-102F 591-2x01-107F 591-2x01-113F
9. DRY PACK PACKAGING CONSIST OF A DESICCANT AND HUMIDITY INDICATOR CARD IN A VACUUM SEALED MOISTURE BARRIER BAG, MOISTURE SENSITIVITY LABEL LEVEL 2 (2a for 591-2901-1XXF) ON OUTSIDE OF BAG, AS PER JEDEC STD. 033.
10. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING, AND STORAGE IN ACCORDANCE WITH IPC-A-610.




Part Numbers with the "F" suffix ending are RoHS Compliant.
Example: 591-2001-102F
Packaging is marked with "RoHS Compliant" label or equivalent markings.
Parts can be reflow soldered per RoHS reflow profile, wave soldered,
dip soldered or hand soldered using typical lead-free soldering process
with max 260°C temp. for 5 sec.



TOLERANCE: .004 UNLESS OTHERWISE SPECIFIED
MILLIMETER DIMENSIONS SHOWN FOR REFERENCE ONLY



13 INCH DIA. REEL SPECIFICATIONS



7 INCH DIA. REEL SPECIFICATIONS



**ATTENTION:
OBSERVE PRECAUTIONS FOR
HANDLING ELECTROSTATIC
SENSITIVE DEVICES**

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.			
SCALE: DRAWING SCALE ALL DIM'S IN: INCHES (MM) TOLERANCES: UNLESS OTHERWISE SPECIFIED FRACTIONS: $\pm 1/64$ DECIMALS (.XX): $\pm .02$ DECIMALS (.XXX): $\pm .010$ ANGLES: $\pm 3^\circ$ FINISH:		DRAWING NUMBER C-17429 REV B	
		TITLE SURFACE MOUNT CBI - SQUARE LENS RoHS COMPLIANT	
		MATERIAL	
FSCM 83330		Dialight ●●●●●●●●●● 1501 ROUTE 34 SOUTH FARMINGDALE, NY 07727	
		SHEET I OF I FAMILY TABLES:	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[591-2101-102F](#) [591-2201-102F](#) [591-2801-102F](#) [591-2301-102F](#) [591-2601-113F](#) [591-2201-107F](#) [591-2201-113F](#)
[591-2301-107F](#) [591-2401-107F](#) [591-2001-107F](#) [591-2101-107F](#) [591-2501-113F](#) [591-2801-107F](#) [591-2601-107F](#)
[591-2701-113F](#) [591-2701-107F](#) [591-2801-113F](#) [591-2901-107F](#) [591-2901-113F](#) [591-2901-102F](#)