



Certifications & Ratings

- RoHS compliant
- IP66/IP67
- IK10
- NEMA 4X


Application

The 622 Series Heavy Duty LED Panel Mount Indicators are elegantly designed for a high-end aesthetic paired with sturdy construction. These indicators are non-magnetic, corrosion resistant for both indoor and outdoor use, and secured to prevent dirt, dust, and water penetration. Ideal for a variety of applications such as:

- Main power indication
 - Remote power indication
 - Status indication
 - Maintenance and warning indication
 - Instrumentation
- ... and many more!

Dimensions

inches [mm]



Mechanical Information

Mounting Hole Size:	0.866" (22 mm)
Max Panel Thickness:	0.394" (10 mm)
Mounting Torque:	7.01 lbs-ft (9.5 Nm)

Specifications

Operating Voltage:	3 VDC (external resistor required) 6, 12 & 24 VDC (internal resistor included)
Operating Temp:	-25 °C to +70 °C (-13 °F to 158 °F)
Storage Temp:	-25 °C to +70 °C (-13 °F to 158 °F)
Electrical Connection:	Screw terminals
Housing:	Stainless Steel
Nut:	Stainless Steel

Ordering Information 622 Series

Part Number Guide

RoHS Compliant

6	2	2	-	1	X	X	X	-	3	0	4	F
							Voltage					
							1	3VDC				
							2	6VDC				
							3	12VDC				
							4	24VDC				
					Color							
					● Red	1	0					
					● Green	2	0					
					● Yellow	3	0					
					● Blue	4	0					

Dialight P/N	Color	Voltage (V DC)	Current (mA)	Typical Intensity (mcd)
622-1101-304F	Red	3	15	200
622-1201-304F	Green			250
622-1301-304F	Yellow			350
622-1401-304F	Blue			300
622-1102-304F	Red	6		200
622-1202-304F	Green			250
622-1302-304F	Yellow			350
622-1402-304F	Blue			300
622-1103-304F	Red	12		200
622-1203-304F	Green			250
622-1303-304F	Yellow			350
622-1403-304F	Blue			300
622-1104-304F	Red	24		200
622-1204-304F	Green			250
622-1304-304F	Yellow			350
622-1404-304F	Blue			300

Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for [herein/above/below], Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[622-1301-304F](#) [622-1202-304F](#) [622-1203-304F](#) [622-1204-304F](#) [622-1404-304F](#) [622-1402-304F](#) [622-1104-304F](#)
[622-1103-304F](#) [622-1102-304F](#) [622-1201-304F](#) [622-1101-304F](#) [622-1403-304F](#) [622-1304-304F](#) [622-1302-304F](#)
[622-1401-304F](#) [622-1303-304F](#)